

Universal Laptop USB Docking Station with VGA Audio Ethernet

Product ID: USBVGADOCK2



The USBVGADOCK2 is a TAA-compliant combination USB VGA adapter and 4-in-1 docking station that converts a single USB 2.0 port into multiple connection ports, including: a VGA port, 10/100 RJ45 network connection, dual (3.5mm phono) audio ports and four additional USB 2.0 ports.

Compatible with a broad range of operating systems, including Microsoft Windows® 7, the USB VGA adapter/docking station supports 1600x1200 (32-bit) display resolutions for connected VGA monitors and saves the time and hassle of having to disconnect devices like speakers and USB peripherals (scanners, printers, webcams etc.) in order to re-connect them to another computer. Using this convenient docking station makes it as simple as creating the single USB 2.0 host connection in order to access the connected peripherals.

The USBVGADOCK2 is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add video outputs to a laptop or small form factor computer without adding or replacing the video card
- Add video, USB, Ethernet and Audio from a single USB connection, without having to open the computer system

Features

- TAA Compliant
- External monitor connection via a VGA port
- Maximum VGA video resolution up to 1600x1200 at 32-bit color
- Speaker and Microphone support via 3.5mm stereo mini-jacks
- 10/100Mbps RJ-45 Ethernet port
- Built-in 4-port USB 2.0 hub
- High Speed USB 2.0 compliant with transfer rates up to 480Mbps
- Small, portable form factor
- Includes a universal power adapter with power connectors for North America, United Kingdom, and Europe

Hardware	Warranty	3 Years	
	4K Support	No	
	Audio	Yes	
	Bus Type	USB 2.0	
	Chipset ID	SMSC - LAN9500 Trigger - UV-185CB-128	
	Displays Supported	1	
	Fast-Charge Port(s)	No	
	Industry Standards	IEEE 802.3, IEEE 802.3u	
Performance	Compatible Networks	10/100 Mbps	
	Full Duplex Support	Yes	
	Maximum Analog Resolutions	1600x1200 @ 32 bits Lower resolutions are also supported.	
	Maximum Data Transfer Rate	10/100 Mbps (Ethernet) 480 Mbps (USB 2.0)	
	Type and Rate	USB 2.0 - 480 Mbit/s	
Connector(s)	Connector Type(s)	1 - RJ-45 Female 1 - USB Mini-B (5 pin) Female 1 - VGA (15 pin, High Density D-Sub) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 4 - USB Type-A (4 pin) USB 2.0 Female	
	OS Compatibility	Windows® 10 (32-bit or 64-bit), 8 / 8.1 (32-bit or 64-bit), 7 (32-bit or 64-bit), Vista (32-bit or 64-bit), XP (32-bit or 64-bit)	
	Power	Center Tip Polarity	Positive
		Input Voltage	115V-230V AC
		Output Current	3A
Output Voltage		5 DC	
Plug Type		M	
Power Consumption (In Watts)		15	
Power Source		AC Adapter Included	
Environmental	Operating Temperature	15°C to 30°C (59°F to 86°F)	
	Storage Temperature	0°C to 70°C (32°F to 158°F)	

Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Height	0.8 in [1.9 cm]
	Product Length	8 in [20.3 cm]
	Product Width	2.7 in [69.8 mm]
	Weight of Product	7.3 oz [208 g]
Packaging Information	Package Height	2.2 in [56 mm]
	Package Length	7.1 in [18 cm]
	Package Width	9.1 in [23.2 cm]
	Shipping (Package) Weight	21.5 oz [608 g]
What's in the Box	Included in Package	1 - USB VGA Dock 1 - 3.3 ft [1016 mm] USB Cable 1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.