

# Multiple Video Input with Audio to HDMI Scaler Switcher - HDMI / VGA / Component

Product ID: VS721MULTI



The VS721MULTI Multiple Video Input to HDMI® Switcher enables users to switch between 7 different audio-video sources to a single HDMI-equipped display.

This versatile switcher is the perfect solution for combining digital and analog video sources (RGB/YPbPr/YCbCr) with your digital HDMI® display, eliminating the cost of upgrading individual components (i.e. DVD player, PC, VCR, etc.).

An all-in-one multimedia solution, the video converter/switcher includes support for full high definition 1080p video resolution as well as digital and analog audio. Plus, the switch features RS232 remote serial control, and includes a convenient IR remote control for switching between video sources .

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Convert analog and digital video to HDMI® for a variety of applications such as switching between consumer electronics devices (e.g. Blu-ray Disc™ players, satellite receivers, video game consoles and other devices)

### Features

- Supports analog PC Resolution input and output up to WUXGA (1920x1200) @ 60Hz
- HDMI® and HDCP compliant
- Supports analog HDTV RGB/YPbPr/YCbCr input, output up to 1080p @ 60Hz

<b>Hardware</b>	Warranty	2 Years
	Audio	Yes
	AV Input	Component
		Composite
		HDMI
		S-Video
		VGA
	AV Output	HDMI
Cabling	HDMI	
Industry Standards	High Speed HDMI®, HDCP	
Ports	7	
<b>Performance</b>	Maximum Analog Resolutions	VGA: 1920x1200 YPbPr: 1920x1080
	Maximum Digital Resolutions	1920x1200
	Supported Resolutions	Support VGA mode 640x480, 720x400, 800x600, 848x480, 1024x768, 1152x864, 1280x720, 1280x768, 1280x800, 1280x960, 1280x1024, 1360x768, 1400x1050, 1440x900, 1440x1050, 1600x1200, 1680x1050, 1920x1080, 1920x1200  Support YPbPR mode 720x480, 720x576, 720x480, 720x576, 1280x720, 1920x1080, 1920x1080
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	3 - HDMI (19 pin) Female  1 - VGA (15 pin, High Density D-Sub) Female  1 - Component Video (3 x RCA) Female  1 - S-Video (4 pin, Mini-DIN) Female  1 - Composite Video (1 x RCA) Female  3 - RCA Female  1 - 3.5 mm Mini-Jack (3 Position) Female
	Connector B	HDMI (19 pin) Female
<b>Software</b>	OS Compatibility	Windows® 10 (32/64), 8/8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows® Server 2008 R2, 2003(32/64)
<b>Indicators</b>	LED Indicators	1 - 1 - HDMI

		1 - 2 - HDMI
		1 - 3 - HDMI
		1 - 4 - VGA
		1 - 5 - YPbPr
		1 - 6 - CVSB
		1 - 7 - S-VIDEO
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.6 A
	Input Voltage	100 - 240 AC
	Output Current	1.5 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	18
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0% to 95% RH Non-Condensing
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-20°C to 85°C (-4°F to 185°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Aluminum
	Product Height	1.8 in [4.5 cm]
	Product Length	15.1 in [38.4 cm]
	Product Width	6.8 in [17.3 cm]
	Weight of Product	4 lb [1.8 kg]
<b>Packaging Information</b>	Package Height	3.5 in [90 mm]
	Package Length	18.1 in [45.9 cm]
	Package Width	10.2 in [26 cm]
	Shipping (Package) Weight	6 lb [2.7 kg]
<b>What's in the Box</b>	Included in Package	1 - multiple format to HDMI audio video switch
		1 - IR remote control
		1 - mounting kit

- 1 - RS232 serial cable (6 ft.)
- 1 - RS-232 control software CD
- 1 - universal power adapter (NA, EU, UK, AU)
- 1 - instruction manual

---

Product appearance and specifications are subject to change without notice.