

6U 30cm (12in) Deep Wall Mounting Bracket for Patch Panel

Product ID: WALLMOUNT6



The WALLMOUNT6 6U 14 in. Deep Wall Mounting Bracket for Patch Panel delivers a sturdy and dependable equipment storage option, allowing you to wallmount equipment for a more efficient and accessible operating environment.

The mounting bracket features an all-steel design and is suitable for mounting patch panels, or other slim 19in equipment to a wall.

Backed by a StarTech.com Lifetime warranty.

**Certifications, Reports
and Compatibility**



Applications

- Wall mount patch panels and other slim 19" rackmount equipment

Features

- Sturdy cold rolled steel construction
- 6U rack height
- 20 kg (44 lbs) weight capacity

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	Special Features	Ships Fully Assembled
		U-Markings
	Wall-Mountable	
	U Height	6U
	Wallmountable	Yes
Performance	Weight Capacity	44.2 lb [20 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
	Enclosure Type	Steel
Product Measurements	Maximum Mounting Depth	13.6 in [34.6 cm]
	Product Height	10.7 in [27.3 cm]
	Product Length	13.8 in [35.1 cm]
	Product Width	19.6 in [49.8 cm]
	Weight of Product	6.4 lb [2.9 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	11.8 in [30 cm]
	Package Length	20.6 in [52.4 cm]
	Package Width	15 in [38 cm]
	Shipping (Package) Weight	4.4 lb [2 kg]
What's in the Box	Included in Package	1 - 6U Wall Mount Rack
		12 - M6 Screws
		12 - M6 Cage Nuts
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.