

Wall-Mount Bracket for Shallow Rack-Mount Equipment - Solid Steel - 8U

Product ID: WALLMOUNT8



This wall-mount bracket provides 8U of space for mounting shallow rack-mount equipment that's 12 in. deep or less to the wall, such as patch panels or network switches.

Improve efficiency and accessibility in your workspace

The 8U rack optimizes your working space by efficiently mounting your shallow equipment on your wall instead of taking up desk space or other usable surface areas. It's the perfect solution for your space-limited SoHo (small office, home office) environment or server room because it doesn't take up any floor space.

Ensure a secure and hassle-free installation

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your mission-critical equipment. Also, because the wall rack's mounting holes are positioned 16 in. apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring.

The rack also features a rear access panel that can be used to easily run cabling into the rack.

Cage nuts and screws are included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

If you're looking for a shallow mounting solution with fewer or more rack units, StarTech.com also offers a [6U wall-mount bracket](#), and a [12U wall-mount bracket](#).

The WALLMOUNT8 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount equipment that is up to 12 inches deep on your wall
- Organize cabling or equipment in your network closet, wiring closet, back office or IDF
- Save space in your SoHo (small office, home office) or server room, by mounting equipment to the wall instead of taking up floor space

Features

- Improve efficiency in your office or server room by mounting shallow equipment to the wall
- Sturdy installation of mission-critical equipment, with a solid steel design
- Hassle-free setup with wall mounting holes spaced 16 in. apart, matching standard dry-wall framework
- Cage nuts and screws included
- Rear access panel for cable management
- 8U wall-mount design

Hardware	Warranty	Lifetime
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Rack Type	2-Post
	U Height	8U
	Wallmountable	Yes
Performance	Weight Capacity (Stationary)	80.2 lb [36.3 kg]
Physical Characteristics	Color	Black
	Internal Height	13.5 in [342.9 mm]
	Internal Width	17.7 in [449.7 mm]
	Product Height	14.3 in [362.5 mm]
	Product Length	13.7 in [349.3 mm]
	Product Weight	12.5 lb [5.7 kg]
	Product Width	20.5 in [520.7 mm]
Packaging Information	Shipping (Package) Weight	17.8 lb [8.1 kg]
What's in the Box	Included in Package	1 - wall-mount bracket
		24 - M5 cage nuts
		24 - M5 screws with washers
		1 - M6 K-nut
		6 - wood screws
		1 - instruction manual

Product appearance and specifications are subject to change without notice.