

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Black

Product ID: WIR5ECMRBK



The WIR5ECMRBK 1000 ft Cat5e Riser Bulk Cable meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable black PVC jacket that enables you to color code your network cable drops as needed for a more organized installation. Bulk packaging is perfect for custom length runs and allows you to cover the exact distance required for your installations.

Constructed of only top quality materials, the WIR5ECMRBK delivers reliable performance and is backed by our Lifetime Warranty.

Riser Rated

This Category 5e cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

100% Copper - a better value

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

24 AWG Wire

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifications, Reports and Compatibility



Applications

- Can be used in riser installations (in-wall, between floor, elevator shaft, etc.)
- Designed for use with Fast Ethernet networks

Features

- UL Listed CMR Riser Fire Rating
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components
- High quality 24 AWG copper wire
- Foot-marked cable

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Fire Rating	CMR Rated (Riser)
	Number of Conductors	4 Pair UTP
Performance	Cable Rating	CAT5e - 350 MHz
Physical Characteristics	Cable Length	1000 ft [304.9 m]
	Color	Black
	Conductor Type	Solid Copper
	Product Length	1000 ft [304.9 m]
	Product Weight	19.8 lb [8.9 kg]
	Wire Gauge	24 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	21.9 lb [9.9 kg]
What's in the Box	Included in Package	1 - 1000 ft Bulk Roll of Black CMR Cat5e Solid UTP Cable

Product appearance and specifications are subject to change without notice.