

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Gray

Product ID: WIRC5ECMRGRY



The WIRC5ECMRGRY Cat5e 350MHz Solid UTP Cable (Gray) is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000-foot bulk roll. The cable features a gray PVC jacket, which provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Ideal for network installation at home, office, or educational institution
- CMR rated for use in walls, conduit, ceiling and other vertical applications

Features

- UL Listed CMR Riser Fire Rating
- Rated up to 350Mhz to provide superior performance and bandwidth over the standard 100Mhz Category 5e specifications
- Flexible PVC rated jacket
- 24 AWG solid bare copper conductor
- 4-pair unshielded twisted pair (UTP) cable
- Foot-marked cable

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Fire Rating	CMR Rated (Riser)
	Industry Standards	Category 5 CMR
	Number of Conductors	4 Pair UTP
Performance	Maximum Cable Length	1000 ft [304.9 m]
Physical Characteristics	Cable Length	1000 ft [304.9 m]
	Color	Gray
	Conductor Type	Solid Copper
	Product Height	0.2 in [5 mm]
	Product Length	1000 ft [304.9 m]
	Product Weight	324.8 oz [9200 g]
	Product Width	0.2 in [5 mm]
Wire Gauge	24 AWG	
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	21.4 lb [9.7 kg]
What's in the Box	Included in Package	1 - 1000 ft Bulk Roll of Gray CMR Cat5e Solid UTP Cable

Product appearance and specifications are subject to change without notice.