

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Gray

Product ID: WIRC6PATGRRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

Features

- Available in various colors for easy identification and color-coding

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Fire Rating	CM Rated
	Number of Conductors	4 pair UTP
Performance	Cable Rating	CAT6 - 500 MHz
Physical Characteristics	Cable Length	1000 ft [304.9 m]
	Color	Gray
	Conductor Type	Stranded Copper
	Product Length	1000 ft [304.9 m]
	Product Weight	29.3 lb [13.3 kg]
	Wire Gauge	24 AWG
Packaging Information	Shipping (Package) Weight	29.3 lb [13.3 kg]
What's in the Box	Included in Package	1000ft Roll Grey Stranded Cat 6 Patch Cable

Product appearance and specifications are subject to change without notice.