

Cat5e Patch kabel met snagless RJ45 connectors - 1,8 m - blauw

Product ID: RJ45PATCH6



The 45PATCH6BL Cat5e Patch Cable (6 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

100% Copper - a better value

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

24 AWG Wire

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

50-micron Gold Connectors

This RJ45 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, Reports and Compatibility



Applications

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Features

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

Hardware	Warranty	Lifetime
	Aantal geleiders	4 Pair UTP
	Brandbestendigheid	CM goedgekeurd
	Type kabel	Snagless
	Type kabelmantel	PVC - Polyvinyl Chloride
Prestaties	Kabelspecificatie	CAT5e - 350 MHz
Connector(en)	Connector A	1 - RJ-45 Mannelijk
	Connector B	1 - RJ-45 Mannelijk
Fysieke eigenschappen	Draaddikte	24 AWG
	Gewicht product	2.4 oz [68 g]
	Kabellengte	6 ft [1.8 m]
	Kleur	Blauw
	Lengte product	6 ft [1.8 m]
Verpakkingsinformatie	Package Height	0.5 in [12 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Verzendgewicht (verpakt)	2.7 oz [77 g]
Wat wordt er meegeleverd	Meegeleverd	1 - 6 Ft Blue RJ45 Cat. 5E Patch cable

Product appearance and specifications are subject to change without notice.