

## 2.5in eSATA USB External Hard Drive Enclosure for SATA HDD

Product ID: SAT2510U2E



This eSATA/USB External Hard Drive Enclosure transforms virtually any 2.5in SATA (SATA, SATA II, SATA III) laptop hard drive or solid state drive (SSD) into the perfect portable storage solution!

Ideal for storing digital multimedia and other demanding applications, the external HDD enclosure lets you get the most out of your hard drive, connecting to a host computer using USB 2.0 (also backward compatible with USB 1.1) or eSATA, for maximum data transfer rates of up to 3Gbps (using eSATA). Large capacity drives (tested with up to 1TB) can be used to greatly enhance your computer's storage/backup capabilities.

A truly portable solution, SAT2510U2E features lightweight, yet durable aluminum construction, as well as a small form factor design that fits perfectly into your pocket or notebook bag when not in use. And, to eliminate the hassle of having to find a power outlet when you are ready to back up your data or load your stored files, the enclosure offers USB powered operation, requiring no external power supply.

### Certifications, Reports and Compatibility



### Applications

- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on extra storage to almost any USB enabled computer system
- Backup important data to an external storage device
- Share large files between computers quickly and securely without a network
- Retrieve data from old SATA drive, or turn the unused drive into additional external storage space

### Features

- SATA revision 2 compliant eSATA host interface, with supported transfer rates up to 3 Gbps
- High Speed USB 2.0 host interface, with supported transfer rates up to 480 Mbps
- Powered directly from the USB port
- Light-weight and durable aluminum chassis
- Power/Activity LED indicator
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" form factor SATA hard drives (HDD) or solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- Includes a protective carrying pouch

<b>Hardware</b>	Warranty	2 Years
	Chipset ID	JMicron - JM20316
	Compatible Drive Types	SATA
	Drive Installation	Fixed
	Drive Size	2.5in
	Fan(s)	No
	Interface	USB 2.0 & eSATA
	Number of Drives	1
<b>Performance</b>	Max Drive Capacity	Currently tested with up to 1TB 5400 RPM hard drives
	Maximum Data Transfer Rate	eSATA - 3Gbps USB 2.0 - 480Mbps
	RAID	No
	UASP Support	No
<b>Connector(s)</b>	Connector Type(s)	1 - eSATA (7 pin, Data) Plug 1 - USB Mini-B (5 pin) Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Indicators</b>	LED Indicators	1 - Single LED, flashes to show drive activity
<b>Power</b>	Input Voltage	5 DC
<b>Physical Characteristics</b>	Color	Silver
	Enclosure Type	Aluminum
	Max Drive Height	0.4 in [9.5 mm]
	Product Height	0.6 in [1.5 cm]
	Product Length	5.3 in [13.5 cm]
	Product Width	2.8 in [70 mm]
	Weight of Product	3.2 oz [90 g]
<b>Packaging Information</b>	Package Height	1.6 in [40 mm]
	Package Length	7.7 in [19.5 cm]
	Package Width	6.1 in [15.5 cm]
	Shipping (Package) Weight	0.7 lb [0.3 kg]
<b>What's in the Box</b>	Included in Package	1 - 2.5" SATA Enclosure 1 - eSATA Cable

- 1 - USB Cable
- 1 - USB to DC Cable
- 1 - Screws
- 1 - Screw Driver
- 1 - Travel Pouch
- 1 - Instruction Manual

---

Product appearance and specifications are subject to change without notice.