




Now Available!
Dual Drive Enclosures



- Double external storage capacity
- Fast data transfers provide a seamless operating experience (E-SATA up to 3 Gbps, USB 2.0 up to 480Mbps)
- Slide-out tray design offers quick insertions/removals, with the added security of a locking door arm
- Lightweight design includes carrying handle for maximum portability

 **Dual 3.5" Drive eSATA to SATA Hard Drive Enclosure**
 StarTech.com ID: [ESATCASE2](#)

 **Dual 3.5" Drive USB2.0 to SATA Hard Drive Enclosure with USB Hub**
 StarTech.com ID: [SATCASE2U2](#)

 **Dual 3.5" Drive USB2.0 to SATA Hard Drive Enclosure with RAID**
 StarTech.com ID: [SATCASE2U2R](#)



How to Sell External Storage to Your Customers



The Opportunity:

External drive enclosures offer users a versatile storage solution - For desktop users, the additional storage offers the data capacity required for advancing multimedia standards. For notebook users, an external drive enclosure offers additional storage, while retaining the portability offered by a laptop computer.


Key Questions to Identify an Opportunity

- Q: Does your current system design limit expandability?** (Our enclosures accommodate IDE and SATA hard drives)
- Q: Do you require a more efficient way to store and backup multimedia files?** (See enclosures that hook up directly to USB device without PC, or have built-in flash card readers)
- Q: Does your data require frequent backups or archiving to an external hard drive?** (One Button Backup feature allows you to make redundant backups/archives at the touch of a button)
- Q: Do you want more storage capacity without sacrificing portability?** (Smaller 2.5" hard drive enclosures are lightweight and convenient to carry)

Why StarTech.com?

- Wide selection of enclosures:** Support for all hard drive sizes and types
- Versatile innovation:** Features such as USB "On-the-go", One-Button Backup, hot-swappable multi-drive RAID, built-in USB hubs and more
- Industry leading value:** Solid aluminum construction and broad functionality combine for maximum cost-effectiveness
- Space saving designs:** Slim models and vertical stands

INFO SAFE
 Products have been Featured in:



SATA: Serial ATA hard drives offer faster data transfers, making them the hard drive of choice.

IDE: IDE (Parallel ATA) hard drives have a proven track record

Why purchase SATA?

- Faster data transfer rate up to 150 Mbps (now 300 Mbps with SATA 300 drives) vs. max. 133 Mbps with IDE.
- Hot-swappable for faster installation
- Thinner cabling simplifies system integration

See reverse side for product line list ▶



Removable and External Storage Solutions

SATA



DRW115SATBK

Drive Type	Style	Construction	Color	Features	Extras Available	Part Number
Serial ATA	Value	Plastic	Beige	3Gb/s Transfer	Caddy	DRW110SAT
Serial ATA	Value	Plastic	Black	3Gb/s Transfer	Caddy	DRW110SATBK
Serial ATA	Rugged	Plastic, Aluminum	Beige	3Gb/s Transfer	Caddy	DRW113SAT
Serial ATA	Rugged	Plastic, Aluminum	Black	3Gb/s Transfer	Caddy	DRW113SATBK
Serial ATA	Durable	Aluminum	Beige	3Gb/s Transfer	-	DRW150SAT
Serial ATA	Durable	Aluminum	Black	3Gb/s Transfer	-	DRW150SATBK
Serial ATA	Professional	Aluminum	Beige	3Gb/s Transfer	Caddy	DRW115SAT
Serial ATA	Professional	Aluminum	Black	3Gb/s Transfer	Caddy	DRW115SATBK
Serial ATA	Fast Swap	Aluminum	Black	3Gb/s Transfer	-	HSB100SATBK

IDE

Retail-Ready



DRW113ATABK

Drive Type	Style	Construction	Color	Features	Extras Available	Part Number
IDE ATA 133	Value	Plastic	Beige	Shock Absorbers	Caddy	DRW110ATA
IDE ATA 133	Value	Plastic	Black	Shock Absorbers	Caddy	DRW110ATABK
IDE ATA 133	Rugged	Plastic, Aluminum	Beige	Hot Swap Software	Caddy	DRW113ATA
IDE ATA 133	Rugged	Plastic, Aluminum	Black	Hot Swap Software	Caddy	DRW113ATABK
IDE ATA 133	Durable	Aluminum	Beige	Cableless Connector	-	DRW150ATA
IDE ATA 133	Durable	Aluminum	Black	Cableless Connector	-	DRW150ATABK
IDE ATA 133	Professional	Aluminum	Beige	Max. Durability	Bay, Caddy	DRW115ATA
IDE ATA 133	Professional	Aluminum	Black	Max. Durability	Bay, Caddy	DRW115ATABK

SCSI / Serial Attached SCSI (SAS)

Retail-Ready



DRW150SCABK

Drive Type	Style	Construction	Color	Features	Extras Available	Part Number
U320 68 Pin	Durable	Aluminum	Beige	2 DBB Fans	-	DRW150SCSI
U320 68 Pin	Durable	Aluminum	Black	2 DBB Fans	Caddy	DRW150SCSIBK
80 Pin SCA	Durable	Aluminum	Beige	2 DBB Fans	-	DRW150SCA
80 Pin SCA	Durable	Aluminum	Black	2 DBB Fans	-	DRW150SCABK
SAS / SATA	Durable	Aluminum	Black	3 Gb/s Transfer	-	DRW150SASBK

Retail-Ready

IDE/SCSI External Drive Enclosures



IDECASE25OTG

Drive Type	Drive Size	Connection	Construction	Color	Features	Part Number
IDE	1.8"	USB 2.0	Aluminum	Silver	One-Button Backup	IDECASE18U2B
IDE	2.5"	USB 2.0	Aluminum	Silver	On-the-Go Technology	IDECASE25OTG
IDE	2.5"	USB 2.0	Aluminum	Silver	One-Button Backup	IDECASE25U2B
Serial ATA	2.5"	USB 2.0	Aluminum	Silver	On-the-Go / SATA HD	SATCASE25OTG
IDE	3.5"	USB 2.0	Aluminum	Silver	One-Button Backup	IDECASE35U2B
IDE	3.5"	USB 2.0	Aluminum	Silver	Card Reader / USB Hub	IDECASEU2CRH
IDE	3.5"	USB 2.0 / RJ45	Aluminum	Silver / Black	NAS	IDECASE35NAS
IDE	3.5"	USB 2.0 / FW400	Aluminum	Silver	Combo	IDECASE35U2F
IDE	3.5"	USB 2.0, FireWire 800	Plastic / Steel	Silver / Black	Combo	IDECASEU2FB
Serial ATA	3.5"	Serial ATA	Aluminum	Silver	SATA HD	IDECASE35SAT
Serial ATA	3.5"	USB 2.0	Aluminum	Silver	SATA HD	SATCASE35U2
IDE	5.25"	USB 2.0	Aluminum	Silver	HDD/CD/DVD	IDECASE525U2
IDE	5.25"	USB 2.0	Plastic	Silver / Black	CD / DVD / DVD-RW	IDESLIMDVU2

Retail-Ready

SATA Backplanes



IDECASE35U2B

Drive Type	Style	Construction	Color	Features	Extras Available	Part Number
Serial ATA	2 Bay	Aluminum	Black	3 Hard Drives	Tray	SATABAY3BK
Serial ATA	3 Bay	Aluminum	Beige	4 Hard Drives	Tray	SATABAY4
Serial ATA	3 Bay	Aluminum	Black	4 Hard Drives	Tray	SATABAY4BK
Serial ATA	3 Bay	Aluminum	Black	5 Hard Drives	Tray	SATABAY5BK

SCSI Backplanes



SATABAY5BK

Drive Type	Style	Construction	Color	Features	Extras Available	Part Number
Serial ATA	Backplane	Aluminum	Beige	3 Hard Drives	Tray	RAIDBAY3
Serial ATA	Backplane	Aluminum	Black	3 Hard Drives	Tray	RAIDBAY3BK

Last updated Nov. 28th, 2006

For complete product information
Visit www.startech.com/drivecases

For Customer Service Call
1-800-265-1844

