

A KVM to Fit Any Configuration

Complete lineup

StarTech.com Desktop KVM Switches offers to fit any situation. Our breadth of product offerings ensures you will find the exact KVM you need for any types of connections you may have.

Reliable

Our Desktop KVM Switches can help eliminate unnecessary downtime by providing a consistently reliable operating experience.



2 Port USB VGA Cable KVM Switch with Audio SV215MICUSBA



4 Port USB KVM Switch with Ethernet Switch Audio & USB 2.0 Hub SV431USBAN



4 Port StarView USB Console KVM switch with OSD SV431DUSB



2 Port Dual DVI USB KVM Switch with Audio SV231DVIDDU

USB

Ports	Input Interface	Video Type	Audio	Accessory Cables	Features	Part Number
2 Port	USB	VGA	Yes	Built-In	KVM on a cable, Hot key + push button	SV215MICUSBA
2 Port	USB	VGA	Yes	Included	Kit	SV211KUSB
2 Port	USB	VGA	-	Included	Professional Series	SV231USB
2 Port	USB	VGA	Yes	Included	Built in ethernet network switch	SV231USBAN
2 Port	USB	VGA	Yes	USBVGA4N1Ax(6, 10)	Hot key, 2 port, 2.0 USB Hub	SV231USBA
2 Port	USB	DVI	Yes	Built-In	KVM on a cable, Hot key + push button	SV215MICDVIA
2 Port	USB	DVI	Yes	Included	Kit	SV211KDVIA
2 Port	USB	DVI	Yes	USB DVI4N1Ax(6, 10,15)	Hot key, 2 port, 2.0 USB Hub	SV231UADVI
4 Port	USB	VGA	Yes	Included	Built in ethernet network switch	SV431USBAN
4 Port	USB	DVI Dual-Link	Yes	USB DVI4N1Ax(6, 10,15)	Ultra High resolution	SV431DVIUAHR
4 Port	USB	VGA	Yes	Included	Kit	SV411KUSB
4 Port	USB	VGA	Yes	USBVGA4N1Ax(6, 10)	Hot key, 2 port, 2.0 USB Hub	SV411USBA
4 Port	USB	DVI	Yes	USB DVI4N1Ax(6, 10,15)	4 port USB 2.0 USB Hub	SV431DVIUA
4 Port	USB	DVI	Yes	USB DVI4N1Ax(6, 10,15)	Independent audio switching	SV431UADVI
4 Port	USB	VGA	-	SVUSB2N1_x(6,10,15)	Professional Series, Rackmount	SV431USB
4 Port	USB	VGA	Yes	SVUSB2N1_x(6,10,15)	Professional Series, Rackmount	SV431USBAE

Retail-Ready

PS/2

Ports	Input Interface	Video Type	Audio	Accessory Cables	Features	Part Number
2 Port	PS/2	VGA	-	Included	Kit	SV211K
2 Port	PS/2	VGA	-	Built-In	KVM on a cable	SV221MICRO
2 Port	PS/2	VGA	-	Included	Small footprint vertical tower	SV211KT
2 Port	PS/2	VGA	Yes	Included	Kit	SV211KA
2 Port	PS/2	DVI	-	DVIISM6 + KXT102MM	Hot key + push button	SV221DVI
2 Port	PS/2	VGA	-	SVPS23N1_x(6,10,15)	Professional Series	SV231
4 Port	PS/2	VGA	-	Included	Kit	SV411K
4 Port	PS/2	VGA	-	Included	Small footprint vertical tower	SV411KT
4 Port	PS/2	VGA	Yes	Included	Kit	SV411KA
4 Port	PS/2	DVI	-	DVIISM6 + KXT102MM	Professional Series, Rackmount	SV421DVI
4 Port	PS/2	VGA	-	SVPS23N1_x(6,10,15)	Professional Series, Rackmount	SV431

USB & PS/2 Hybrids

Retail-Ready

Ports	Input Interface	Video Type	Accessory Cables	Features	Part Number
4 Port	PS/2	VGA	SVPS23N1_x(6,10,15) or SVUSB2N1_x(6,10,15)	Professional Series	SV431H
4 Port	USB	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	Professional Series	SV431DUSB

Retail-Ready

Dual Display KVMs

Ports	Input Interface	Video Type	Audio	Accessory Cables	Part Number
2 Port	PS/2	Dual Displays VGA + VGA	-	SVPS23N1_x(6,10,15) + MXT101MMHQ	SV221DD
2 Port	PS/2	Dual Displays DVI + DVI	-	DVIISM6 + KXT102MM	SV221DVIDD
2 Port	USB	Dual Displays VGA + DVI	Yes	USB DVI4N1Ax(6, 10,15) + MXT101MMHQ	SV231DDUSB
2 Port	USB	Dual Displays DVI + DVI	Yes	USB DVI4N1Ax(6, 10,15) + DVIDSMx(10,15)	SV231DVIDDU
4 Port	PS/2	Dual Displays VGA + VGA	-	SVPS23N1_x(6,10,15) + MXT101MMHQ	SV421DD
4 Port	PS/2	Dual Displays DVI + DVI	-	DVIISM6 + KXT102MM	SV421DVIDD
4 Port	USB	Dual Displays VGA + DVI	Yes	USB DVI4N1Ax(6, 10,15) + MXT101MMHQ	SV431DDUSB
4 Port	USB	Dual Displays DVI + DVI	Yes	USB DVI4N1Ax(6, 10,15) + DVIDSMx(10,15)	SV431DVIDDU

Retail-Ready



Broad Compatibility, Maximum Reliability



Reliable and Affordable

Built for durability and longevity, StarTech.com Enterprise KVM Switches provide a consistently reliable user experience, and are backed by warranty, and free technical support.

Complete Solutions

StarTech.com KVM switches include unique, all-in-one devices, for control of your entire server room.



Enterprise KVM (Rackmount)

Output Plug	Input Plug	Ports	Video	Accessory Cables*	Details	Part Number
USB + PS/2	PS/2	8 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV831HD
USB + PS/2	USB + PS/2	8 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV831DUSB
USB + PS/2	USB + PS/2	8 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	With Audio	SV831DUSBA
PS/2	PS/2	8 Port	VGA	SVPS23N1_x(6,10,15, 25, 35, 50)	-	SV831
USB + PS/2	PS/2	16 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV1631HD
USB + PS/2	USB + PS/2	16 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV1631DUSB
USB + PS/2	PS/2	8 Port	VGA	SV5PS2S or SV5USBS (available in 4 & 8 packs)	CAT5	SV831DUTP
USB + PS/2	PS/2	16 Port	VGA	SV5PS2S or SV5USBS (available in 4 & 8 packs)	CAT5	SV1631DUTP
PS/2	PS/2	8 Port	VGA	SVPS23N1_x(6,10,15)	Dual User	SV832DS
PS/2	PS/2	16 Port	VGA	SVPS23N1_x(6,10,15)	Dual User	SV1632DS



8 Port StarView USB Console KVM switch with OSD
SV831DUSB

Retail-Ready

KVM over IP / Remote Server Management (Rackmount)

Output Plug	Input Plug	Ports	Video	Accessory Cables*	Details	Part Number
USB	USB	1 Port	VGA	Included	USB 2.0 Virtual Media	SV1107IPEXT
USB + PS/2	USB + PS/2	1 Port	VGA	Included + USB2HAB6	USB 2.0 Virtual Media	SV1115IPEXT
USB + PS/2	PS/2	4 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV441HDIE
USB	USB	4 Port	VGA	Included (optional SVUSBSVGAx(6,10))	USB 2.0 Virtual Media	SV441DUSBI
USB + PS/2	PS/2	8 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV841HDIE
USB + PS/2	PS/2	16 Port	VGA	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	-	SV1641HDIE
USB + PS/2	USB + PS/2	16 Port	VGA	SWITSV5PS2M or SWITSV5USBM	USB 2.0 Virtual Media	SV1653DXI
USB + PS/2	USB + PS/2	32 Port	VGA	SWITSV5PS2M or SWITSV5USBM	USB 2.0 Virtual Media**	SV3254DX4I
Serial RJ45	RJ45	16 Port	-	GC98FF + M45PATCHxBL (3,6,10,15)	Serial Console Server	ECS0016
N/A	Serial DB9	8 Outlet	-	-	Serial Controlled	PCM815SHNA



16 Port Enhanced RS232 Serial Console Server
ECS0016

Retail-Ready

Rackmount LCD Console

KVM Ports	Video Size	Accessory Cables*	Details	Part Number
1 Port	15"	SVPS23N1_x(6,10,15,25) or USBEXTAA_x(6,10)	Lockable LCD	RACKCONS1501
1 Port	17"	SVPS23N1_x(6,10,15,25) or USBEXTAA_x(6,10)	Lockable LCD	RACKCONS1701
8 Port	17"	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	Lockable LCD	RACKCONS1708
16 Port	17"	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	Lockable LCD	RACKCONS1716
1 Port	19"	SVPS23N1_x(6,10,15,25) or USBEXTAA_x(6,10)	Lockable LCD	RACKCONS1901
16 Port	19"	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	Lockable LCD	RACKCONS1916
1 Port	17"	SVPS23N1_x(6,10,15,25)	Professional Series - Modular	1UCABCONS17
1 Port	19"	SVPS23N1_x(6,10,15,25)	Professional Series - Modular	1UCABCONS19
16 Port	17"	SVECONUSx(6, 10, 15) or SVECONx(6, 10, 15)	Over IP, Professional Series - Modular	CABCONS1716I



1U 17in Rackmount LCD Console with Integrated 16 Port IP KVM Switch
CABCONS1716I

Retail-Ready

Universal KVM Cables

KVM Connectors	PC Connectors	Length	Part Number
USB+VGA	USB+VGA	6, 10, 15 ft.	SVUSB2N1_x (6,10,15)
USB+DVI+SPKR+MIC	USB+DVI+SPKR+MIC	6, 15 ft.	USBDVI4N1Ax (6,15)
DB15	USB+VGA	6, 10, 15 ft.	SVECONUSx (6,10,15)
DB15	PS/2+VGA	6, 10, 15, 25, 50 ft.	SVECONx (6,10,15,25,50)
PS/2+VGA	PS/2+VGA	6, 10, 15, 25, 35, 50 ft.	SVPS23N1_x (6,10,15,25,35,50)
PS/2+VGA	PS/2+VGA	6, 10, 15, 25, 50 ft.	PS23N1THINx (6,10,15,25,50)



6 ft 4-in-1 USB DVI KVM Cable with Audio and Microphone
USBDVI4N1A6

Retail-Ready

Last updated April 20th, 2009

For complete product information
Visit www.startech.com/KVM

For Customer Service Call
1-800-265-1844

