


## Composite and S-Video to VGA Video Converter for Computer Monitors

StarTech ID: COMP2VGA



This Composite and S-Video to VGA Video Converter lets you play console video games on your computer monitor! With StarTech.com's for Computer Monitors Video Game Jockey, there's no more waiting to use the TV. Simply connect your Xbox®, Playstation 2®, GAMECUBE™, Dreamcast™, or other game console to the Video Game Jockey, then plug into your computer monitor, and it's game on!

An economical solution that saves the expense of a separate TV and frees up your workspace, the Composite/S-Video to VGA converter supports full audio pass through via your PC speakers or headphones and switches from PC to game display with the push of a button - the adapter even works when the computer is powered off!

A versatile video solution, the Composite/S-Video to VGA converter is also a great way to connect VCRs, DVD players and camcorders to your monitor.

Backed by StarTech.com's 1-year warranty.

### Applications and Solutions

- Connects any commercial game console or VCR/DVD to a VGA monitor

## Features

- Also allows VCRs, DVDs and video cameras to connect to monitor
- Audio pass through with amplified (active) speakers
- Compatible anywhere in the world, with automatic NTSC and PAL video signals detection
- Convenient push-button switching between game display and PC display
- Easy one-time plug and play set up requires no drivers
- Includes all necessary cables for instant out of the box set up
- Superior video resolution - 1280 x 1024 @ 60Hz
- Supports composite (RCA) and S-video input

## Technical Specifications

- Color: Black
- Connector Types: 1 - High Density 15 pin Male
- Connector Types: 3 - RCA Female
- Connector Types: 1 - Phono 3.5 mm Female
- Connector Types: 1 - 4 DIN Female
- Input Voltage: 9
- Maximum Analog Resolutions: 1280 x 1024
- Power Adapter Included: Yes
- Power Adapter - Amperage: (0.6A)
- Power Adapter - DC Voltage: DC 9
- Carton Quantity: 10
- Shipping (Package) Weight: 1.88 lb [0.85 kg]
- Connectors: 1 x Male DB15 VGA In
  - 1 x Female DB15 VGA Monitor Out
  - 2 x RCA composite Audio In, 3.5mm line in and speaker out
  - 1 x RCA composite Video In
  - 1 x S-Video In
- Power Supply: DC 9V power adapter included
- Cables Included: 1 x HDDB15-pin extension cable
  - 1 x 3.5mm stereo audio cable
- Output Frequency NTSC: Horizontal = 31.4685KHzVertical = 60 HzResolution = 720 x 480
- Output Frequency PAL: Horizontal = 31.25 KHzVertical = 50 HzResolution = 720 x 576
- Product Length: 6.5 in [165 mm]
- Product Width: 3.98 in [101 mm]
- Product Height: 0.98 in [25 mm]

- Product Weight: 0.5 lb [0.23 kg]