

4 Port DVI Video Splitter / Distribution Amplifier

StarTech ID: ST124DVI



This DVI splitter lets you share DVI video signals between four displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source, while maintaining high definition display resolutions up to 1080p.

A simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments), the DVI splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

Designed to provide dependable performance, the DVI splitter/signal distribution amplifier is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Connect DVI enabled projectors, monitors, plasma screens, commercial billboards, and wall display systems
- Great for use in tradeshow, POS, healthcare, airport, train station and bus terminal settings
- Ideal for graphic design, classroom use and training seminars

Features

- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Fully compliant with the DVI 1.0 standard established by the DDWG
- Simple setup for quick connection in minutes
- Supports resolutions of up to 1600 x 1200 pixels @ 60 Hz

Technical Specifications

- Color: Gray
- Connector Types: 3 - DVI-I Dual Link Female
- Product Height: 1.65 in [42 mm]
- Input Current: 1.5
- Input Voltage: 7.5
- Product Length: 10.55 in [268 mm]
- Maximum Analog Resolutions: 1600 x 1200
- Number of Ports: 4
- Carton Quantity: 10
- Shipping (Package) Weight: 4.24 lb [1.92 kg]
- Product Weight: 43.77 oz [1240 g]
- Product Width: 4.13 in [105 mm]
- Video Bandwidth: 25 ~ 165 MHz (VGA ~ UXGA)
- Max Resolution: 1600 x 1200 @ 60Hz
- Input Connector: 1 x 24-pin DVI-I
- Output Connector: 2 x 24-pin DVI-I
- LED Indicators: 1 x Power
- Power Adapter: 7.5V DC (1.5A)
- Length: 10.5 Inches (268 mm)
- Width: 4.25 Inches (105 mm)
- Height: 1.65 Inches (42 mm)
- Weight: 2.6 lbs (1.24 kg)
- Industry Standards: DVI 1.0
- Cable Distance - Source to Display: Max of 33ft (10m)
- Note that this product is not intended for use with widescreen displays.