

6-in-1 Black USB 2.0 Laptop Docking Station with Port Replicator

StarTech ID: USB6N1DOCK



This 6-in-1 USB Laptop Docking Station can be connected to a laptop or desktop USB 2.0 port, to add several other commonly used interface ports.

Through a single USB 2.0 connection to the host computer, you can add a parallel port, a serial port, PS/2 mouse and keyboard ports, a Fast Ethernet LAN connection (10/100Mbps/sec), and two USB 2.0 ports.

A highly scalable solution, the Laptop Docking Station can be daisy chained with additional hubs or docking stations for increased device connectivity. The docking station is USB 2.0 certified by the USB-IF ensuring compatibility and full USB 2.0 capability when connected to a USB 2.0 host system, and is backward compatible with USB 1.1 devices.

Designed with mobility in mind, the laptop docking station is compact and lightweight, making it an ideal laptop accessory.

Applications and Solutions

- Connect serial, parallel, USB, Ethernet and PS/2 devices to your system
- Has the ability to create a direct USB-to-USB data exchange channel between two computers

Features

- Adds a Parallel, Serial, 10/100 Mbits/sec Ethernet LAN, PS/2 Keyboard/Mouse and two USB 2.0 ports to your laptop or desktop system
- Backward compatible with USB 1.1 devices
- Easy Plug and Play installation
- Occupies only one USB port, while providing ample connectivity
- USB 2.0 certified by the USB-IF
- Users can add on/daisy chain additional hubs or docking stations for increased connectivity

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Connector Types: 1 - USB B Female
- Connector Types: 2 - USB A Female
- Connector Types: 1 - DB25 Female
- Connector Types: 1 - DB9 Male
- Connector Types: 2 - DIN 6 Female
- Connector Types: 1 - RJ45 Female
- Enclosure Type: Plastic
- Product Height: 0.98 in [2.5 cm]
- Product Length: 7.01 in [17.8 cm]
- Operating Temperature: 0 to 50
- Power Adapter Included: Yes
- Power Adapter - Amperage: 2.5A
- Power Adapter - DC Voltage: 5V DC
- Center Tip Polarity: Positive
- Carton Quantity: 20
- Industry Standards: USB 2.0
- Industry Standards: IEEE 1294
- Industry Standards: IEEE 802.3
- Industry Standards: USB 1.1
- Storage Temperature: -20 to 70
- USB-IF Certified: Yes

- Shipping (Package) Weight: 1.28 lb [0.58 kg]
- Product Weight: 5.65 oz [160 g]
- Product Width: 2.17 in [5.5 cm]
- Power: Bus Powered or Self Powered

