



Broad compatibility, maximum reliability

Conserve Space

Our enterprise KVM switches are designed to save valuable work space while allowing control of multiple computers from a centralised command point

Reliability

Built for durability and longevity, StarTech.com enterprise KVM switches provide a consistently reliable user experience

Cost-effective

StarTech.com KVM switches allows you to eliminate the unnecessary expense of having to purchase duplicate peripherals



Enterprise KVM Switches

# of Ports	Interface	Rackmount	Video Type	On Screen Display	SKU Number
4	PS/2	Yes	VGA	-	SV431GB
4	USB + PS/2	Yes	VGA	-	SV431HGB
4	USB	Yes	VGA	-	SV431USBGB
4	PS/2	Yes	VGA	Yes	SV431DGB
4	PS/2	-	VGA	-	SV421DD
4	PS/2	-	DVI	-	SV421DVI
4	PS/2	-	DVI	-	SV421DVIDD
8	PS/2	Yes	VGA	-	SV831GB
8	USB + PS/2	Yes	VGA	Yes	SV831HDGB
16	USB + PS/2	Yes	VGA	Yes	SV1631HDGB



4 Port StarView DVI KVM Switch with Dual Display SV421DVIDD

Retail-Ready

Reduce wasted server rack space & increase performance

Space saving solutions

DuraView rack consoles centralize control inputs into a tidy, compact solution

Maximum compatibility

Designed for use with optional KVM additions, DuraView gives you the room you need to grow

Durability

DuraView rack consoles are designed to provide long lasting outstanding performance, while withstanding normal wear and tear



DuraView Rack Consoles

Display Size	Interface	Rackmount	Features	SKU Number
15	PS/2	Yes	TFT Display, Cables included	CABCONS8GB
15	PS/2	Yes	TFT Display, Cables included	CABCONS16GB
15	PS/2	Yes	TFT Display, Cables included	1UCABCONSGB



1U LCD Rack / Cabinet Console with 15 in. TFT Screen 1UCABCONSGB

Retail-Ready

DuraView KVM Modules

# of Ports	Interface	Rackmount	On Screen Display	SKU Number
8	USB + PS/2	Yes	Yes	CAB831HD
8	PS/2	Yes	Yes	CAB832DS
16	USB + PS/2	Yes	Yes	CAB1631HD



16 Port Multi-Platform USB & PS/2 KVM Switch Module CAB1631D1U

Retail-Ready

Last updated Jan. 10th, 2007

For complete product information
Visit www.startech.com/kvm

For Customer Service Call
00-800-7827-8324





Make the most of valuable desk space

Compact

StarTech.com desktop KVM switches are built to take up minimal desk space, while still providing broad functionality

Reliable

Our desktop KVM switches can help eliminate unnecessary downtime, by providing a consistently reliable operating experience

Complete Solutions

Desktop KVM switches are designed for easy installation and many include the necessary cabling to help simplify deployment & configuration



2 Port Micro Built-on-Cable KVM Switch
SV221MICRO



4 Port StarView Tower Style KVM Switch
SV411KT

Desktop KVM Switches

# of Ports	Interface		Video Type	Audio	SKU Number
2	PS/2	Two 3-in-1 tangle free cables	VGA	-	SV211K
2	PS/2	Two 3-in-1 tangle free cables	VGA	Yes	SV211KA
2	PS/2	Two 3-in-1 tangle free cables	VGA	-	SV211KT
2	PS/2	Built-on-cables	VGA	-	SV221MICRO
2	PS/2 + Serial	-	VGA	-	SV231
2	USB	Two 2-in-1 tangle free cables	VGA	-	SV231USBGB
2	PS/2	-	VGA	-	SV221DD
2	PS/2	-	DVI	-	SV221DVI
2	PS/2	-	DVI	-	SV221DVIDD
4	PS/2	Four 3-in-1 tangle free cables	VGA	-	SV411K
4	PS/2	Four 3-in-1 tangle free cables	VGA	Yes	SV411KA
4	PS/2	Four 3-in-1 tangle free cables	VGA	-	SV411KT

Retail-Ready

KVM Cables

Description	Lengths available	SKU Number
PS/2 ULTRA-THIN 3-IN-1 KVM CABLE	6, 10, 15, 25, 50	PS23N1THINxx
PS/2-STYLE 3-IN-1 KVM SWITCH CABLE	6, 10, 15, 25, 35, 50	SVPS23N1_xx
USB+VGA 2-IN-1 KVM SWITCH CABLE	6, 15	SVUSB2N1_xx

xx = length Retail-Ready



PS/2 Ultra-Thin 3-in-1 KVM Cable
PS23N1THINxx

