


**10 Pack of 1 Port PCI RS232 Serial Adapter Card with 16550 UART**

*StarTech ID: 10PKPCI1S550*



x 10

This bulk (10) package of (16C550) Serial PCI Cards offers a cost-saving solution for adding Serial connectivity to multiple computers.

StarTech.com's 16550 Serial PCI Card can be installed in a PCI slot to add an RS232 serial port - a cost-effective solution for connecting any new serial device or old legacy serial device, with data transfer rates of up to 115.2 Kbps.

Perfect for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system, the adapter card supports IRQ sharing and operates flawlessly with Windows® XP, Server 2003, 2000, ME, 98, 95, NT4, 3.1, DOS® and Linux®.

The Serial PCI card can be connected in minutes through simple plug and play installation and is backed by StarTech.com's lifetime warranty and FREE LIFETIME tech support.

## Applications and Solutions

- **Casino** (video lottery terminals, slot machines)
- **Consumer** (modems, PDAs, digital cameras, printers)
- **Environmental Control** (lighting, temperature, clocks)
- **Healthcare** (patient monitoring equipment, nurses' stations, modems)
- **Hospitality/Restaurant** (credit card/debit card reader, serial printers)
- **Hotel Front Desk** (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- **ISDN Networking**
- **Manufacturing** (CNC machinery, process control equipment, bar code scanners, serial printers)
- **POS** (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- **Security** (UPS control, access key panels, video cameras, card readers, modems)
- Great for OEMs, system builders or IT professionals requiring quantity serial cards for mass installations or upgrades

## Features

- 16 byte FIFO buffer ensures fast data transfer while multitasking
- Includes drivers for Linux® and all versions of Windows®
- Supports the RS-232 serial interface and the PCI bus interface

## Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI (5 Volt)
- Chipset ID: NetMos NM9820CV
- Maximum Data Transfer Rate: 920000 Kbits/Sec
- Number of Ports: 1
- Package Quantity:: 10
- Carton Quantity: 50
- Shipping (Package) Weight: 1.83 lb [0.83 kg]
- Communication Buffer: 16 Byte FIFO
- Connector Types: 1 - DB9 Male
- Bus Type: PCI 2.1
- Serial Ports: 1 x 16C550
- OS Compatibility: DOS, Windows 95/ 98SE/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.4.x and up  
Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS

