

### Added functionality, increased productivity

#### Wide Selection


Quickly find the right PCI Express product for any application, to optimize system performance

#### Speed






























StarTech.com can help you harness the speed and enhanced capabilities offered by PCI Express, in turn maximizing your system productivity

#### Reliability

All of our PCI Express cards feature a lifetime warranty and offer free technical support









#### I/O Cards

# of Ports	Type	Bus	Data Rate	Part Number
1 Port	16550 Serial	PCI Express	230.4 Kbps	PEX1S550 
2 Port	16550 Serial	PCI Express	230.4 Kbps	PEX2S550 
2 USB, 3 FireWire 800	Combo	PCI Express	480 Mbps, 800 Mbps	PEX3U3F800 
1 Port Parallel, 2 Port Serial	Combo	PCI Express	230.4 Kbps, 1.5 Mbps	PEX2S1P 
PCI-e to ExpressCard 34/54	Adapter	PCI Express	-	PEX2EC 
PCI-e ExpressCard 34/54	Adapter	PCI Express	-	PEX2ECDP 
1 Port	Parallel	PCI Express	1.5 Mbps	PEX1PECP 
2 Port	Parallel	PCI Express	1.5 Mbps	PEX2PECP 
4 Port	USB 2.0	PCI Express	480 Mbps	PEX400USB2 
1 Port	Express Card	PCI Express	-	PEX2EC 
2 Port	Firewire	PCI Express	400 Mbps	PEX1394A2 
3 Port	Firewire	PCI Express	400 Mbps	PEX13943 
3 Port	Firewire	PCI Express	800 Mbps	PEX1394B3 
2 Port SATA	Serial ATA	PCI Express	300 Mbps	PEXSATA22I 
1 Internal, 1 External	eSATA / SATA	PCI Express	300 Mbps	PEXESATA2I 
4 Port	16C950	PCI Express	115.2 Kbps	PEX45950 
2 Port	16C950	PCI Express	460 Kbps	PEX25950 
8 Port	16C950	PCI Express	921.6 Kbps	PEX8S950LP 
2 Port	eSATA	PCI Express	300 Mbps	PEXESATA2 
1 IDE	IDE	PCI Express	133 Mbps	PEX2IDE 
2 SATA, 1 IDE	SATA/IDE	PCI Express	300 Mbps	PEXSAT2IDE2 
1 DVI, 1 DB15, 1 S-Video	GeForce 7200GS	PCI Express	-	PEXVID7200A 
1 Port	eSATA	PCI Express	300 Mbps	PEXESATAI 
PCI-e to PCI Exp Bay	Expansion Bay	PCI Express	-	PEX2PCI4 
1 RJ45 Port	10/100	PCI Express	-	PEX100S 
x1 to x16	Slot Extension	PCI Express	-	PEX1T016 
1 Port	Parallel	PCI Express	460.8 Kbps	PEX1S552 
2 Port	Parallel	PCI Express	460.8 Kbps	PEX2S552 
2 Port	Parallel	PCI Express	460.8 Kbps	PEX2S5521P 

 Retail-Ready

#### Power Supplies

Wattage	MTBF	Fan	ATX 12V	Mb Support	DC Output / Connectors	SKU Number
400	100,000	Dual Ball Bearing	2.01	24/20 pin	Dual 12V / PCI-E / SATA	ATX2PW400PRO 
450	100,000	Dual Ball Bearing	2.01	24/20 pin	Dual 12V / PCI-E / SATA	ATX2PW450PRO 
500	100,000	Dual Ball Bearing	2.01	24/20 pin	Dual 12V / PCI-E / SATA	ATX2PW500PRO 
550	100,000	Dual Ball Bearing	2.01	24/20 pin	Dual 12V / 2 PCI-E / SATA	ATX2PW550PRO 
400	100,000	Silent 120 mm	2.01	24/20 pin	Dual 12V / PCI-E / SATA	ATX2POW400HS 
500	100,000	Silent 120 mm	2.01	24/20 pin	Dual 12V / PCI-E / SATA	ATX2POW500HS 

 Retail-Ready

#### Cables

Description	Part Number
PCI Express adapter for use with standard power supply connector	LP4PCIEXADAP 
3ft PCI Express 1x External Cable	PCIE1X3 

 Retail-Ready



2 Port 16550 PCI-E WHQL Approved Serial Card PEX2S550



2 Port 16550 PCI Express Serial Card PEX2S550



400 Watt Professional ATX12V 2.01 Power Supply with PCI Express and SATA ATX2PW400PRO



LP4 to 6 pin PCI Express Video Card Power Adapter LP4PCIEXADAP

Last updated May. 15th, 2008

For complete product information  
Visit [www.startech.com](http://www.startech.com)

Fast, Friendly Support your way!



Phone Support  
1-800-265-1844



Email Support  
sales@startech.com



Chat Online  
[www.startech.com](http://www.startech.com)

