

POS Solution Helper

Learn what questions to ask to help your customers complete their next POS solution.



If answer is YES to any of these questions, the customer requires a product from the category listed to the right

▶ See reverse for StarTech.com category products ▶

Card Reader



Connect:

1. Do you require a USB hub or card (PCI/PCI Express)?
2. How many ports do you require?

Extend:

1. Do you need to connect these at further distances from the computer or branch server?

▶ **Expand** ▶

▶ **Extend** ▶

▶ **Connect** ▶

Handheld/Mounted Scanners



Connect:

1. Do you require USB or Serial connectivity?
2. Is your customer looking for an internal solution (PCI cards) or external solution (USB Hubs)?
3. Do you need to convert serial devices for USB connectivity?

Extend:

1. Do you need to connect these at further distances from the computer or branch server?

▶ **Expand** ▶

▶ **Convert** ▶

Display



Connect:

1. Do you require Serial connectivity for the touch screen?
2. Is your customer looking for an internal solution (PCI cards)?
3. Does your customer require an external solution to convert serial devices to USB connectivity?

Extend:

1. Do you need to connect these at further distances from the computer or branch server?

▶ **Expand** ▶

▶ **Extend** ▶

▶ **Connect** ▶

Printer







Connect:

1. Do you require parallel, serial, or USB connectivity?


▶ **Expand** ▶




Expand

StarTech.com ID		
Serial Cards		
	PCI1S550	1 Port 16550 Serial PCI Card
	PCI1S550_LP	1 Port 16550 Serial PCI Card - Low profile
	PCI2S550	2 Port 16550 Serial PCI Card
	PCI2S550_LP	2 Port 16550 Serial PCI Card - Low profile
	PCI2S1P	2 Port 16550 Serial + 1 Port Parallel PCI Card
	PCI4S550	4 Port 16550 Serial PCI Card (Breakout version)
	PEX1S550	1 Port 16550 Serial PCI Express Card
	PEX2S550	2 Port 16550 Serial PCI Express Card
	PCI1S950DV	1 Port PCI 16950 RS-232 Dual Voltage / Dual Profile Serial Card
	PCI2S950DV	2 Port PCI 16950 RS-232 Dual Voltage / Dual Profile Serial Card
Parallel Cards		
	PCI1P	1 Port Parallel PCI Card
	PCI1PECP	1 Port EPP/ECP Parallel PCI Card
	PCI1P_LP	1 Port EPP/ECP Parallel PCI Card - Low profile
	PCI1PECPDV	1 Port Parallel Dual Voltage / Dual Profile PCI Card
	PCI2PECP	2 Port EPP/ECP Parallel PCI Card
	PEX1PECP	1 Port EPP/ECP PCI-Express Parallel Card
USB Cards		
	PCI220USB	2 Port USB 2.0 PCI Card
	PCI220USBLP	Low Profile 2 Port PCI USB 2.0 Card (2+1 internal ports)
	PCI420USB	4 Port USB 2.0 PCI Card
	PEX400USB2	4 Port USB 2.0 PCI Express Card
Networking Cards		
	ST100S	10/100 Ethernet PCI Card
	ST100SLP	10/100 Ethernet PCI Card - Low profile
	ST1000BT32	10/100/1000 Ethernet PCI Card - 32-bit
	ST1000BTPEX	PCI Express 10/100/1000Mbps Gigabit Ethernet Card
	USB2105S	USB 2.0 to 10/100 Mbps Ethernet Adapter


Convert

StarTech.com ID		
	ICUSB232	1 Port USB to RS-232 Serial DB9 Converter
	ICUSB232C2	2 Port USB to RS-232 Serial Converter (built-on-cable)
	ICUSB232_4	4 port USB to RS-232 Serial DB9 Converter
	ICUSB1284	USB to Parallel Interface Converter

Extend

StarTech.com ID		
	NETRS232_1/2/4	1/2/4 Port RS-232 Serial IP Extender
	RS232EXTC5	1 Port RS-232 Serial CAT5 Extender – 1000m
	USB110EXT	1 Port Bus Powered 165 Foot (50 Meter) Multi-Speed USB Extender
	USB120EXT	2 Port Bus Powered 165 Foot (50 meter) Multi-Speed USB Extender

Connect

StarTech.com ID		
	USB2HAB1	1' High Speed USB 2.0 Cable
	USBEXTAA_6	6' Fully Rated USB Extension Cable
	MXT100	6' DB9 Serial Cable (M-F)
	MXT100FF	6' DB9 Serial Cable (F-F)
	PB10	10' Parallel Printer Cable
	SCNM925FM	10' Serial Null Modem Cable DB9F-DB25M
	KXT102	6' PS/2 Keyboard/Mouse Extension Cable
	45PATCH3BK	3' CAT5 Patch Cable - Black
	POS4510C	Shielded RJ45 POS Scanner Cable
	POSDB945P	DB9 to RJ45 POS Scanner Cable
	KYC1MF	6" PS/2 Keyboard Splitter Cable 2F-1M

