



Added functionality, increased productivity

Wide Selection

Quickly find the right card for any application, to optimize system performance

Functionality

StarTech.com can help you add options and capability to your computer, helping to maximise system productivity

Dependable

All of our I/O cards are covered under warranty and offer free, lifetime technical support



USB



4Port USB 2.0 PCI Card
PCI420USB

# of Ports	Bus	Type	Data Rate	Notes	Part Number
2 Ports	PCI	USB 2.0	480Mbps	-	PCI220USB
2 Ports	PCI	USB 2.0	480Mbps	Value Card	PCI225USB
2 Ports	PCI Low Profile	USB 2.0	480Mbps	-	PCI225USB_LP
4 Ports	PCI	USB 2.0	480Mbps	-	PCI420USB
4 Ports	PCI	USB 2.0	480Mbps	Value Card	PCI425USB
6 Ports	PCI	USB 2.0	480Mbps	-	PCI625USB2I
2 Ports	Cardbus	USB 2.0	480Mbps	-	CBUSB2
2 Ports	Cardbus	USB 2.0	480Mbps	-	CBUSB220

Retail-Ready



4Port IEEE-1394 FireWire PCI Card with Digital Video Editing Kit
PCI1394_4

FireWire

# of Ports	Bus	Type	Data Rate	Notes	Part Number
2 Ports	PCI	FireWire	400Mbps	Digital Video Kit Included	PCI1394_2
3 Ports	PCI	FireWire 800	800Mbps	Digital Video Kit Included	PCI1394B_3
2 Ports	PCI	FireWire	400Mbps	Digital Video Kit Included	PCI1394_2LP
4 Ports	PCI	FireWire	400Mbps	Digital Video Kit Included	PCI1394_4
3 Ports	Cardbus	FireWire	400Mbps	Digital Video Kit Included	CB1394
2 Ports	Cardbus	FireWire	400Mbps	Digital Video Kit Included	CB1394_2

Retail-Ready



2Port 16550 Serial and 1Port EPP/ ECP Parallel Slot Saver PCI Card
PCI2S1P

Combo

# of Ports	Bus	Type	Data Rate	Part Number
2 Serial, 1 ECP/EPP Parallel	PCI	Combo	115Kbps, 1.5Mbps	PCI2S1P
3 USB, 2 FireWire	PCI	Combo	480Mbps, 400Mbps	PCI3UV22F
2 Serial, 1 Parallel	PCI Express	Combo	230.4Kbps, 1.5Mbps	PEX2S1P

Retail-Ready



Dual Channel Serial ATA PCI Controller Card
PCISATA2

Serial ATA

# of Ports	Bus	Type	Data Rate	Part Number
1 Internal, 1 External	PCI	Serial ATA	150 Mbytes/s	PCISATA2EXT
4 Port RAID 0,1	PCI	Serial ATA	150 Mbytes/s	PCISATA4R1

Retail-Ready



Dual Channel Ultra ATA/133 IDE PCI Card
PCI2IDE133

IDE

# of Ports	Bus	Type	Data Rate	Part Number
Dual Channel	PCI	Ultra ATA/133 IDE	133 Mbytes/s	PCI2IDE133

Retail-Ready

Last updated Jan. 15th, 2007

For complete product information
Visit www.startech.com/iocards

For Customer Service Call
00-800-7827-8324





Solutions for...

Industrial / Enterprise

We supply a wide range of I/O cards designed for applications in industrial settings

Consumer / Small Business

StarTech.com offers a broad selection of I/O cards designed to connect today's hottest peripherals



2 Port 16550 Serial PCI Card
PCI2S550



Dual Profile 4 Port RS-232
Powered 16650 Serial PCI Card
PCI1S650PW



2 Port 16550 PCI Express
Serial Card
PEX2S550



2 Port RS-232 Serial Ethernet IP
Adapter (Device Server, Console
Server)
NETRS232_2GB



1 Port EPP/ECP Parallel PCI
Card
PCI1PECP

Serial

# of Ports	Bus	Type	Data Rate	Notes	Part Number
PCI, ISA and CardBus					
1 Port	PCI	16550 Serial	115.2 Kbits/sec	-	PCI1S550
2 Port	PCI	16550 Serial	115.2 Kbits/sec	-	PCI2S550
4 Port	PCI	16550 Serial	115.2 Kbits/sec	Value Card	PCI4S550N
1 Port	PCI	16550 Serial	115.2 Kbits/sec	10 Pack	10PKPCI1S550
2 Port	PCI	16550 Serial	115.2 Kbits/sec	10 Pack	10PKPCI2S550
2 Port	PCI	16550 Serial	115.2 Kbits/sec	Low Profile	PCI1S550_LP
2 Port	PCI	16550 Serial	115.2 Kbits/sec	Low Profile	PCI2S550_LP
1 Port	ISA	16550 Serial	115.2 Kbits/sec	-	ISA1S550
2 Port	ISA	16550 Serial	115.2 Kbits/sec	-	ISA2S550
2 Port	PCI	16950 Serial UART	115.2 Kbits/sec	-	PCI2S950
2 Port	PCI	RS-422/RS-485	921.6 Kbits/sec	-	PCI2S422DB9
2 Port	PCI	RS-422/RS-485	921.6 Kbits/sec	Optically Isolated	PCI2S422ISO
2 Port	Cardbus	RS-232	921.6 Kbits/sec	-	CB2S650
3.3/5.0 V Compatible					
2 Port	PCI	16550 Serial	115.2 Kbits/sec	3.3/5.0V compatible	PCI2S5503V
1 Port	PCI	16650 Serial	920 Kbits/sec	Powered Card	PCI1S650PW
2 Port	PCI	16650 Serial	920 Kbits/sec	Powered Card	PCI2S650PW
4 Port	PCI	16650 Serial	920 Kbits/sec	3.3/5.0V, WHQL	PCI1S650DV
2 Port	PCI	16650 Serial	920 Kbits/sec	3.3/5.0V, WHQL	PCI2S650DV
PCI Express					
1 Port	PCI Express	16550 Serial	230.4 Kbits/sec	-	PEX1S550
2 Port	PCI Express	16550 Serial	230.4 Kbits/sec	-	PEX2S550
2 Port	PCI Express	16650 Serial	920 Kbits/sec	WHQL	PEX2S650
4 Port	PCI Express	16650 Serial	920 Kbits/sec	WHQL	PEX4S650
Serial Over IP					
1 Port	Serial Ethernet Adapter	RS-232	115.2 Kbits/sec	-	NETRS232_1GB
2 Port	Serial Ethernet Adapter	RS-232	115.2 Kbits/sec	-	NETRS232_2GB
4 Port	Serial Ethernet Adapter	RS-232	115.2 Kbits/sec	-	NETRS232_4GB

Parallel

# of Ports	Bus	Type	Data Rate	Features	Part Number
1 Port	PCI	EPP/ECP Parallel	1.5 Mbps	-	PCI1PECP
2 Port	PCI	EPP/ECP Parallel	1.5 Mbps	-	PCI2PECP
1 Port	PCI	EPP/ECP Parallel	1.5 Mbps	Low Profile	PCI1P_LP
1 Port	PCI	EPP/ECP Parallel	1.5 Mbps	3.3/5.0v	PCI1PECP3V
1 Port	PCI	EPP/ECP Parallel	1.5 Mbps	-	PCI1P
1 Port	ISA	EPP/ECP Parallel	1.5 Mbps	-	ISA1P
1 Port	PCI Express	EPP/ECP Parallel	1.5 Mbps	-	PEX1PECP
2 Port	PCI Express	EPP/ECP Parallel	1.5 Mbps	-	PEX2PECP

