

10 Pack 2 Port PCI Serial Adapter Cards

StarTech ID: 10PKPCI2S550



The 10PKPCI2S550 10 Pack 2 Port PCI Serial Adapter Cards lets you deploy serial connectivity across multiple computers, at a competitive price. Ideal for system builders, these cards come in non-retail packaging with a single driver disk, providing you with over 35% in savings!

Each 2 Port 16550 Serial Card can be installed in a PCI slot to add two serial ports - a cost-effective solution for connecting any new or legacy serial device, with data transfer rates of up to 115.2 Kbps.

Perfect for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system, the adapter card supports IRQ sharing and operates flawlessly with Windows® XP, Server 2003, 2000, ME, 98, 95, NT4, 3.1, DOS® and Linux®.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications

- **Manufacturing** (CNC machinery, process control equipment, bar code scanners, serial printers)
- **POS** (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- **Consumer** (modems, PDAs, digital cameras, printers)
- **Security** (UPS control, access key panels, video cameras, card readers, modems)
- **Casino** (video lottery terminals, slot machines)
- **Environmental Control** (lighting, temperature, clocks)
- **Healthcare** (patient monitoring equipment, nurses' stations, modems)
- **Hotel Front Desk** (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- **Hospitality/Restaurant** (credit card/debit card reader, serial printers)
- Great for OEMs, system builders or IT professionals requiring quantity serial cards for mass installations or upgrades
- **ISDN Networking**

Features

- Includes drivers for Linux® and all versions of Windows®
- 16 byte FIFO buffer ensures fast data transfer while multitasking
- Supports the RS-232 serial interface and the PCI bus interface
- Supports data rates up to 115.2 Kbps

Technical Specifications

Warranty	Lifetime
Ports	2
Bus Type	PCI (5 Volt)
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Industry Standards	PCI 2.1
Chipset ID	ASIX/MosChip - MCS9835CV
Connector Type(s)	1 - PCI (5V; 32-bit) Male
External Ports	2 - DB-9 (9 pin; D-Sub) Male
Maximum Data Transfer Rate	115.2 Kbps
Serial Protocol	RS-232
FIFO	16 Byte
OS Compatibility	DOS, Windows 95/ 98SE/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.4.x and up Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS/ CE 5.0/ CE 6.0
Product Length	4.7 in [120 mm]
Product Width	0.8 in [20 mm]
Product Height	4.7 in [120 mm]
Product Weight	2.1 oz [60 g]
Shipping (Package) Weight	2.1 lb [0.9 kg]
Included in Package	10 - PCI2S550 Serial Cards
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

