

## 3.5in Bay Ejectable Multi Memory Card Reader

StarTech ID: 35FCREADREM



Use your flash cards on the go! StarTech.com's 3.5" bay multi-panel gives you a removable flash card reader, plus two USB 2.0 ports, all in the same bay.

The portable 7-in-1 card reader lets you transfer music, pictures, and other data to and from your favorite flash media devices without having to connect them to your computer. Plus, just eject the removable reader from the bay and take card-reading capabilities wherever you go! Accepts the seven most popular formats:

- Compact Flash I/II
- IBM Micro Drives
- Smart Media
- Secure Digital
- Multi-Media
- Memory Sticks
- MS Pro cards

With no need for an external power adapter, the compact removable reader is perfect for lightweight travel. Eliminate the hassle of physically connecting every digital device to your computer, and enjoy card-reading capabilities anywhere, with the FCREADREM from StarTech.com.

## **Applications and Solutions**

- Connect USB 2.0 peripherals to your desktop computer
- Transfer data between your computer and the following supported memory cards formats: Compact Flash I & II, IBM Micro Drive, Smart Media Card, Secure Digital Card, Multi-Media Card, Memory Sticks and MS Pro Card

## Features

- Adds two USB 2.0 ports to your desktop computer with data transfer rates of up to 480 Mbits/sec
- Easily drag and drop files, pictures and music files for editing and storage
- Low power consumption preserves notebook computer battery life
- Panel fits easily into a 3.5" bay on your desktop computer
- Removable card reader portion of the unit connects to a laptop computer through a USB port and requires no external power adapter
- Requires no external power adapter
- USB 2.0 compliant and backward compatible with the USB 1.1 standard
- Works with Compact Flash I & II, IBM Micro Drive, Smart Media Card, Secure Digital Card, Multi-Media Card, Memory Sticks and MS Pro Cards

## Technical Specifications

- Warranty: 1 Year warranty
- Color: Gray
- Connector Types: 2 - USB A Female
- Enclosure Type: Plastic
- Product Height: 1.02 in [26 mm]
- LED Indicators: 1 - Power
- LED Indicators: 1 - Activity
- Product Length: 4.92 in [125 mm]
- Maximum Data Transfer Rate: 480000000 Mbits/Sec
- Memory Media Type: Compact Flash I
- Memory Media Type: Compact Flash II
- Memory Media Type: IBM Micro Drive
- Memory Media Type: Smart Media
- Memory Media Type: Secure Digital Card
- Memory Media Type: Multi Media Card
- Memory Media Type: Memory Stick
- Carton Quantity: 20
- Industry Standards: USB 2.0
- Shipping (Package) Weight: 0.88 lb [0.4 kg]
- Product Weight: 11.3 oz [320 g]

- Product Width: 3.98 in [10.1 cm]
- General Specifications: Windows 98SE/2000/ME/XP/Vista  
Mac OS X and up

