

350 Watt ATX12V 2.01 Dell Replacement Computer PC Power Supply

StarTech ID: ATXPW350DELL



This 350 Watt ATX12V 2.01 Dell PC Power Supply is a reliable upgrade or replacement for many compatible Dell computers (see compatible models below). It offers dual 12V power rails to deliver stable power to demanding components, as well as both 20 and 24-pin ATX motherboard power connectors and a generous number of component connectors to ensure broad system compatibility.

Constructed of high quality components and designed to provide a long-lasting, durable power source for hard-working PCs, the 350 Watt ATX12V 2.01 Dell PC Power Supply is backed by StarTech.com's 2 year warranty and free lifetime technical support.

Dimension Series Models: 3000 / 3100 / 4600 / 4700 / 9100 / E310 / E510

Optiplex Series Model: GX280

Power Edge Series Model: SC420

Precision Workstation Series Model: Model 370

Applications

- Replacement 350W power supply, compatible with certain Dell PC's(see model list on Overview page)
- Upgrade current Dell power supply for more power and support of upgraded 24-pin motherboards and SATA hard drives.

Features

- ATX12V version 2.01 compliant
- EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- 80mm fan provides efficient cooling for the system and the power supply
- High quality connectors provide minimal resistance and enhanced electric conductivity
- Our power supplies are compatible with many of latest Intel P4 and AMD processors
- 20/24 split motherboard connector
- SATA connectors for SATA Hard Drive support

Technical Specifications

Warranty	2 Years
Fans	1 - 80 mm
Fan Bearing Type	Sleeve Bearing
Output Connectors	1 - ATX 12V P4 Power (4 pin; v 2.x) Male
Output Connectors	1 - ATX AUX Power (6 pin; v 1.x) Female
Output Connectors	1 - ATX Split Power (20+4 pin; v 2.x) Male
Output Connectors	1 - SP4 (4 pin; Small Drive Power) Female
Output Connectors	2 - SATA Power (15 pin) Receptacle
Output Connectors	3 - LP4 (4 pin; Molex Large Drive Power) Female
Output Power	350W
MTBF	100,000 Hours
Enclosure Type	Zinc-Plated Casing
Product Length	5.9 in [150 mm]
Product Width	5.5 in [140 mm]
Product Height	3.4 in [86 mm]
Product Weight	4.2 lb [1.9 kg]
Input Voltage Frequency	50~60 Hz
Current -12.0V (A)	0.8A
Current +12.0V1 (A)	10A
Current +12.0V2 (A)	15A
Current +3.3V (A)	22A
Current +5.0V (A)	21A
Current +5.0Vsb (A)	2.5A
Input Voltage	115 ~ 230 AC
Input Current	8 ~ 4 A
Operating Temperature	0° ~ 50°
Storage Temperature	-20° ~ 80°
Shipping (Package) Weight	4.7 lb [2.1 kg]
Included in Package	1 - 350 Watt Dell Power Supply
Included in Package	1 - Standard power cable
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

