

2 Port CardBus Laptop USB 2.0 PC Card Adapter

StarTech ID: CBUSB22



This 2 Port CardBus USB 2.0 Adapter adds two USB 2.0 ports to your laptop or desktop computer, with support for full hi-speed USB data transfer rates of up to 480 Mbps.

The USB 2.0 CardBus adapter offers backward compatibility with USB 1.1 devices, ensuring seamless operation with older USB peripherals and supports hot-swappable operation to provide hassle-free peripheral connections without having to reboot the computer.

Designed to provide a permanent USB 2.0 solution, the CardBus adapter is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

Applications

- Connect all kinds of external USB devices such as cameras, external hard drives, keyboards/mice to a laptop computer
- Add additional USB ports to a laptop to connect more devices
- Upgrade an old laptop with only USB 1.1 ports to be able to use USB 2.0 devices

Features

- High Speed USB 2.0 compliant host interface, with supported transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices
- Provides up to 500mA of power per port, with optional external power adapter
- Support for up to 127 USB devices per port (requires additional USB hubs)
- Plug and Play and Hot Swap compatible

Technical Specifications

Warranty	Lifetime
Ports	2
Interface	CardBus
Bus Type	CardBus (PCMCIA)
Chipset ID	VIA - VT6212
Connector Type(s)	1 - PC Card (Type II; Cardbus)
Connector Type(s)	2 - USB A (4 pin) Female
Maximum Data Transfer Rate	480 Mbps
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.2.x, 10.3.x, 10.4.x
Microsoft WHQL Certified	Yes
Product Length	4.5 in [11.5 cm]
Product Width	2.2 in [5.5 cm]
Product Height	0.6 in [1.5 cm]
Product Weight	0.1 lb [0.1 kg]
Power Adapter Included	Optional
Output Voltage	5 DC
Output Current	1A+
Center Tip Polarity	Positive
Plug Type	H
Operating Temperature	05/9/2012eg;C to 855/9/2012eg;C (325/9/2012eg;F to 1855/9/2012eg;F)
Storage Temperature	-555/9/2012eg;C to 1255/9/2012eg;C (-675/9/2012eg;F to 2575/9/2012eg;F)
System and Cable Requirements	Minimum Processor Requirements: Intel Pentium Pro, Pentium III, P4, or better
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - CardBus USB 2.0 Card
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

