

Composite and S-Video to VGA Video Converter for Computer Monitors

StarTech ID: COMP2VGA



This Composite and S-Video to VGA Video Converter lets you play console video games on your computer monitor! With StarTech.com's for Computer Monitors Video Game Jockey, there's no more waiting to use the TV. Simply connect your Xbox®, Playstation 2®, GAMECUBE™, Dreamcast™, or other game console to the Video Game Jockey, then plug into your computer monitor, and it's game on!

An economical solution that saves the expense of a separate TV and frees up your workspace, the Composite/S-Video to VGA converter supports full audio pass through via your PC speakers or headphones and switches from PC to game display with the push of a button - the adapter even works when the computer is powered off!

A versatile video solution, the Composite/S-Video to VGA converter is also a great way to connect VCRs, DVD players and camcorders to your monitor.

Backed by StarTech.com's 2-year warranty.

Applications

- Connects any commercial game console or VCR/DVD to a VGA monitor

Features

- Compatible anywhere in the world, with automatic NTSC and PAL video signals detection
- Convenient push-button switching between game display and PC display
- Easy one-time plug and play set up requires no drivers
- Audio pass through with amplified (active) speakers
- Supports composite (RCA) and S-video input
- Also allows VCRs, DVDs and video cameras to connect to monitor
- Includes all necessary cables for instant out of the box set up
- Superior video resolution - 1280 x 1024 @ 60Hz

Technical Specifications

Warranty	2 Years
Audio	Yes
Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female
Connector A	1 - Composite Video (1 x RCA) Female
Connector A	1 - S-Video (4 pin; Mini-DIN) Female
Connector A	1 - Stereo Audio (2 x RCA) Female
Connector B	1 - 3.5 mm Mini-Jack (3 Position) Female
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Maximum Analog Resolutions	1280 x 1024
Supported Resolutions	NTSC - 720 x 480 PAL - 720 x 576
Frequency Range	NTSC Horizontal = 31.4685KHz Vertical = 60 Hz PAL Horizontal = 31.25 KHz Vertical = 50 Hz
Color	Black
Product Length	6.5 in [165 mm]
Product Width	4 in [101 mm]
Product Height	1 in [25 mm]
Product Weight	0.5 lb [0.2 kg]
Power Adapter Included	Yes
Input Voltage	100~125 AC
Input Current	0.1 A
Output Voltage	9 DC
Output Current	0.6A
Center Tip Polarity	Positive
Shipping (Package) Weight	1.9 lb [0.9 kg]
Included in Package	1 - Composite/Svideo to VGA Converter
Included in Package	1 - 3.5mm audio cable
Included in Package	1 - VGA cable
Included in Package	1 - AC Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

