

Value 3.5in IDE Hard Drive Mobile Rack for 5.25in Bay

StarTech ID: DRW110ATA



StarTech.com's DRW110ATA is a removable hard drive enclosure featuring unique shock absorbers that offers a cost-effective way to quickly insert or remove ATA hard drives from any PC with an available 5.25-inch drive bay without opening the computer. It is an ideal solution for high-speed back-ups, moving large files from one computer to another, and for running multiple operating systems on the same PC.

While providing security and minimizing downtime, the DRW110ATA features unique shock absorbers that help limit physical damages to the enclosed hard drive during transport.

Applications

- Use multiple operating systems on one computer and share a PC with your kids without worrying about your business data and other valuable information
- Removable drive drawers can be used in homes, at work, offices, schools and in large enterprises
- Fast and easy way to make backup copies of your files, applications, company's critical data and for transporting databases and other large files from one location to another

Features

- Designed for easy installation and maintenance
- Single Ball-Bearing cooling fan provides efficient cooling and increased air flow
- Bay is built with a key lock mechanism to prevent the hard drive from being accidentally removed while in operation
- LED indicators continuously shows operating status
- The frame and caddy is constructed with high quality plastic for maximum durability
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rate
- Secure and affordable solution to store and transfer data

Technical Specifications

| | |
|------------------------|---|
| Warranty | 2 Years |
| Connector Type(s) | 1 - IDE (40 Pin; EIDE/PATA) Female |
| Connector Type(s) | 1 - IDE (40 Pin; EIDE/PATA) Male |
| Connector Type(s) | 1 - LP4 (4 pin; Molex Large Drive Power) Female |
| Connector Type(s) | 1 - LP4 (4 pin; Molex Large Drive Power) Male |
| General Specifications | 1.15 lbs (0.53 kg) |
| General Specifications | 40 Pin Header Female, 4 Pin LP4 Female |
| General Specifications | 40 Pin Header Male, 4 Pin LP4 Male |
| General Specifications | 8.625 x 5.75 x 1.61 Inches (220 x 148 x 41 mm) |
| General Specifications | Any PC or Mac with an IDE Hard Drive interface and an available 5.25 inch drive bay |
| General Specifications | Compatible with all 3.5 inch IDE/ATA Hard Drives up to ATA133 and any operating system |
| General Specifications | FCC Class B |
| General Specifications | If you require the ability to insert/remove drives with the computer running, DRW113ATA includes Swap Manager for Windows |
| General Specifications | One rear-mounted 4cm ball bearing fan |
| General Specifications | Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated |
| General Specifications | Yellow - Drive Activity, Green - Drive Power |
| Color | Beige |
| Enclosure Type | Plastic |
| Product Length | 8.7 in [220 mm] |
| Product Width | 5.8 in [148 mm] |
| Product Height | 1.6 in [41 mm] |
| Product Weight | 18.7 oz [530 g] |
| LED Indicators | 1 - Activity |
| LED Indicators | 1 - Power |
| Shipping (Package) | 1.3 lb [0.6 kg] |

Weight

Fans 1 - 40 mm

Shock Protection Yes

Certifications, Reports and Compatibility

