

DS Series Digital Signage

Allow StarTech.com to help you optimize your digital signage solution with our DS Series digital signage media extension system.

Comprised of the DS128 VGA video broadcaster and DSRXL receiver units, the DS series offers more than just VGA extension, delivering audio and bi-directional serial (RS-232) connectivity to your displays, ensuring your message is delivered to your target audience the way you want it to be seen and heard. Capture attention with HD resolutions and stereo audio at distances up to 300m/950ft.

The DS Series offers our most flexible digital signage system, including network and JAVA-based DSNet Manager software control, which allows you to toggle signals on/off at each receiver, fine tune RGB SKEW calibration and run up to 80 displays with the DS128 (8 port broadcaster) and DSRXL (long range, dual port, daisy chainable receiver).



DS128 Front

Advantages:

- Included DSNet Manager software is cross-platform (Windows®/ Mac®/Linux®)
- Software-controlled RGB SKEW calibration, that can be used over a local area network
- Take control of which signals are sent to the displays and toggle on/off signals to each receiver
- Dual port VGA receivers allow for back to back or side by side displays to help reduce costs on the number of receivers required
- Receivers are daisy chainable and can connect up to 5 receivers using Cat5/6/7 cable



DS128 Back

Receiver Comparison Matrix

Specifications	StarTech.com	Minicom/Cables To Go*	
	DSRXL	Dual Port/Long Range	Short Range
HD Resolution Support**	✓	✓	✓
Distance Support (300m / 950ft)	✓	600m/2000ft	✓
Bi-Directional RS-232	✓	✓	✓
VGA and Stereo Audio	✓	✓	✓
Dual Monitor Receiver	✓	✓	
Daisy Chainable Receiver	✓	✓	
Included RGB SKEW Calibration	✓		
DDC Support	✓	✓	✓
Local Monitor Support	✓	✓	✓
Cross Platform (Windows/Mac/Linux)	✓		
VESA Mounting	✓	✓	✓

* Cables To Go and Minicom product are equivalent

** Resolution varies by distance and cable type. Visit www.startech.com/DS128 for resolution support

QUESTIONS?

PHONE

1-800-265-1844

LIVE CHAT

www.startech.com



Visit our website for complete information on all StarTech.com products.



www.startech.com

DS Series Digital Signage

How it works:

Connect a VGA video output device (PC or Media Player) to the DS128 (8 port broadcaster); from the DS128, you can run Cat5/6/7 cabling to the DSRXL receiver(s), which can be installed at the display, allowing you to distribute VGA video as well as the accompanying audio and serial control signals.

Need to add more displays? The DS128 offers 8 ports for connection to the DSRXL (receiver). The DSRXL offers dual port VGA connection for back-to-back or side-by-side displays. Additionally, each receiver has an RJ45 port for daisy-chaining up to 5 receivers - that's up to a maximum of 80 displays! (See application diagram).



QUESTIONS?
PHONE
1-800-265-1844
LIVE CHAT
www.startech.com



Visit our website for complete information on all StarTech.com products.

www.startech.com