

## 2 Port 1b 1a ExpressCard 34mm Laptop 1394 FireWire Adapter Card

StarTech ID: EC13941A1B



This ExpressCard (34mm) dual port 1394 FireWire Adapter Card features two 1394 Firewire ports (1b, 1a) - adding both FireWire 400 and FireWire 800 connectivity to a laptop computer, with support for virtually any IEEE1394 device - a cost-effective and convenient solution for connecting FireWire devices to your laptop computer.

A convenient video editing solution, the ExpressCard FireWire adapter makes it easy to connect DV camcorders, external hard drives or FireWire audio/video devices to a laptop computer.

Plus, the Adapter card includes Ulead's Video Studio 10 software - ideal for editing video from FireWire devices through a notebook computer.

### Applications and Solutions

- Add a high-speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos and video
- Connect a high-speed external hard drive to an ExpressCard-enabled system

## Features

- One 9-pin FireWire 800 port with transfer rates up to 800Mbps
- One 6-pin FireWire 400 port with transfer rates up to 400Mbps
- Compliant with IEEE 1394b and backward compatible with IEEE 1394a - 2000 as well as 1394-1995 standards
- Optional external power support for high-powered FireWire devices
- Fits in both 34mm and 54mm ExpressCard slots
- Plug-and-Play and hot-swap compatible

## Technical Specifications

- Warranty: 1 Year warranty
- Bus Type: 34mm ExpressCard
- Chipset ID: LSI L-FW643
- Connector Types: 1 - FireWire 6 pin Male
- Connector Types: 1 - FireWire 800 9 pin Male
- Product Height: 0.79 in [20 mm]
- Product Length: 4.53 in [115 mm]
- Number of Ports: 2
- Carton Quantity: 40
- Shipping (Package) Weight: 6.28 oz [178 g]
- Product Weight: 1.09 oz [31 g]
- Product Width: 1.73 in [44 mm]
- Number of Ports: 2 IEEE FireWire Ports (1x 1394A and 1x 1394B)
- Maximum Data Transfer Rate:
  - 1394A - up to 400 Mbps
  - 1394B - up to 800 Mbps
- Optional Power Adapter: 12VDC, 2000+ mA, center positive, type H plug
- Power Adapter Included: No
- OS Compatibility: Windows 2000/ XP(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit), and Mac OS X, and Linux

