

2 Port 1b 1a ExpressCard 34mm Laptop 1394 FireWire Adapter Card

StarTech ID: EC13941A1B



This ExpressCard (34mm) dual port 1394 FireWire Adapter Card features two 1394 FireWire ports (1b, 1a) - adding both FireWire 400 and FireWire 800 connectivity to a laptop computer, with support for virtually any IEEE 1394 device - a cost-effective and convenient solution for connecting FireWire devices to your laptop computer.

A convenient video editing solution, the ExpressCard FireWire adapter makes it easy to connect DV camcorders, external hard drives or FireWire audio/video devices to a laptop computer.

Plus, the Adapter card includes Ulead's Video Studio 10 software - ideal for editing video from FireWire devices through a notebook computer.

Applications

- Add a high-speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos and video
- Connect a high-speed external hard drive to an ExpressCard-enabled system

Features

- One 9-pin FireWire 800 port with transfer rates up to 800Mbps
- One 6-pin FireWire 400 port with transfer rates up to 400Mbps
- Compliant with IEEE 1394b and backward compatible with IEEE 1394a - 2000 as well as 1394-1995 standards
- Optional external power support for high-powered FireWire devices
- Fits in both 34mm and 54mm ExpressCard slots
- Plug-and-Play and hot-swap compatible

Technical Specifications

Warranty	Lifetime
Ports	2
Interface	FireWire 400 (1394a)
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Chipset ID	LSI/Agere - FW643
Connector Type(s)	1 - ExpressCard (34mm)
External Ports	1 - Firewire 400 (6 pin; IEEE 1394a) Female
External Ports	1 - Firewire 800 (9 pin; IEEE 1394b) Female
Maximum Data Transfer Rate	1394A - Up to 400Mbps 1394B - Up to 800Mbps
OS Compatibility	Windows 2000/ XP(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit), and Mac OS X, and Linux
Product Length	4.5 in [115 mm]
Product Width	1.7 in [44 mm]
Product Height	0.8 in [20 mm]
Product Weight	1.1 oz [31 g]
Power Adapter Included	No
Note	Optional power adapter specifications: 12VDC, 2000+ mA, Center positive, Type H plug
Shipping (Package) Weight	6.3 oz [178 g]
Included in Package	1 - ExpressCard FireWire Card
Included in Package	1 - FireWire Cable
Included in Package	1 - Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

