

Spare Hard Drive Caddy for Beige DRW115ATA Mobile Rack

StarTech ID: DRW115CAD



The DRW115CAD is an extra IDE hard drive caddy or carrier for using multiple removable drives on the same system. You can swap operating systems, make high speed, high capacity backups or provide individual hard drives for multiple users. It features a protective shock absorption system, an all aluminum extra rugged construction for extra security and cooling, two front-mounting ball bearing fans to keep your drives at their optimum temperatures and four LED indicators keep you updated on your drive's status, and is Plug and Play compatible with the DRW115ATA.

Applications

- Ideal when using 2 hard drives on one drive drawer bay

Features

- Exclusive shock absorber system protects the hard drive from damage
- Secure and affordable solution to store and transfer data
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rate up to 133 MB/s
- 2 Ball-Bearing fans maintain optimum cooling and increased air flow
- LED indicators continuously show the operating status of the drive drawer
- Key lock mechanism prevents the hard drive from being accidentally removed while in operation

Technical Specifications

Warranty	2 Years
Key Lock	Yes
Fans	2 - 40 mm
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Female
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Male
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
Hot Swap Capability	Yes
General Specifications	
General Specifications	1.4 Lbs (0.64 kg)
General Specifications	2 Ball-Bearing Fans
General Specifications	8.54 x 5.12 x 1.69 Inches (217 x 130 x 43 mm)
General Specifications	All 3.5-Inch IDE Hard Drives
General Specifications	Aluminum
General Specifications	Beige
General Specifications	CE
General Specifications	Green
General Specifications	Normal - Green & Overheat - Red
General Specifications	PC or MAC with a 5.25 Inch DRW115ATA Bay
General Specifications	Red
General Specifications	Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
General Specifications	Yellow
Color	Beige
Enclosure Type	Aluminum
Product Length	9 in [229 mm]
Product Width	5.7 in [145 mm]
Product Height	1.6 in [41 mm]
Product Weight	22.6 oz [640 g]
LED Indicators	1 - Activity
LED Indicators	1 - Fan Failure
LED Indicators	1 - Power
LED Indicators	1 - Temperature Warning
Shipping (Package) Weight	1.6 lb [0.7 kg]

Certifications, Reports and Compatibility

