

## 4 Port PCI 1394a FireWire Adapter Card with Digital Video Editing Kit

StarTech ID: PCI1394\_4



This 4 Port PCI IEEE 1394 FireWire 400 Adapter Card turns a motherboard PCI slot into four IEEE 1394a FireWire 6-pin female ports (1 internal, 3 external) - a cost-effective solution that lets you connect any FireWire 400 device that uses a 6-pin connector to your desktop computer.

The card can be installed in either Mac or PC computers, providing a practical solution for connecting iPods, MP3 players, portable drives, digital camcorders and more. The adapter card supports hot-swappable connectivity, allowing you to plug, unplug, and swap your FireWire peripherals with ease, saving time and hassle.

The 4 port FireWire PCI adapter card includes a copy of ULEAD's VideoStudio SE Basic video editing software, making it easy to capture and edit video from your digital video camcorder.

### Applications

- Add a high-speed FireWire port to a desktop without any FireWire ports
- Connect a digital camera to a desktop with a PCI slot to download photos and video
- Connect a external FireWire hard drive or optical drive to a PCI-enabled system

### Features

- 3 external, 1 shared internal FireWire400 port, with supported data transfer rates up to 400 Mbps
- Compliant with IEEE 1394a - 2000 as well as 1394-1995 standards
- Includes Video Editing kit: Ulead Video Studio SE and FireWire cable
- Plug-and-Play and hot-swap compatible

## Technical Specifications

Warranty	Lifetime
Ports	4
Interface	FireWire 400 (1394a)
Bus Type	PCI (5 Volt)
Card Type	Standard Profile
Industry Standards	IEEE 1394-1995
Industry Standards	IEEE 1394a
Industry Standards	OHCI
Industry Standards	PCI 2.1
Chipset ID	VIA - VT6306
Connector Type(s)	1 - PCI (5V; 32-bit) Male
Internal Ports	1 - Firewire 400 (6 pin; IEEE 1394a) Female
External Ports	3 - Firewire 400 (6 pin; IEEE 1394a) Female
Maximum Data Transfer Rate	400 Mbps
OS Compatibility	Windows 2000/ XP(32/64-bit)/ 2003(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit), Mac OS 8.6 and up, and Linux
Microsoft WHQL Certified	Yes
Product Length	4.7 in [12 cm]
Product Width	0.7 in [18 mm]
Product Height	3.1 in [8 cm]
Product Weight	2.6 oz [75 g]
System and Cable Requirements	Unused PCI slot
<b>Note</b>	The internal port and the top external port cannot be used at the same time. Only one or the other is active at a time.
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - PCI Firewire Card
Included in Package	1 - Firewire cable 4pin-6pin
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

