


3 Port PCI High Speed USB 2.0 Adapter Card

StarTech ID: PCI220USB



This 2 Port PCI USB 2.0 Adapter Card adds three USB 2.0 connections (2 external and 1 internal) to a computer, through simple installation in an available PCI slot.

The PCI USB card offers a cost-effective solution for adding USB peripheral connectivity without having to upgrade the computer motherboard, supporting USB 2.0 devices with full high-speed USB data transfer rates of up to 480Mbps. Plus, the PCI USB card is suitable for connecting older USB devices, based on backward compatibility with USB 1.1 devices.

The PCI-based USB card can be connected to the computer in seconds, through simple WHQL-certified plug-and-play installation, and supports device hot-swapping, allowing you to connect/disconnect USB peripherals without having to power down the computer or reboot.

This high quality USB adapter card is backed by StarTech.com's lifetime warranty and free lifetime technical support.

Applications and Solutions

- Digital cameras
- DVD drives
- External CDR/RWs
- Flash card readers/writers
- Joysticks
- Mice and keyboards
- MP3 players
- Portable hard drives
- Printers
- Scanners
- Webcams

Features

- 40 times faster than USB 1.1
- Backward compatible with USB version 1.1
- Compliant with PCI specification 2.2
- Connect up to 127 devices by cascading multiple hubs
- Easy plug and play installation
- WHQL Certified, designed to work with Microsoft Windows XP

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI / PCI-X (5 / 3.3V)
- Chipset ID: VIA: VT6202
- External Ports: 2 - USB A Female
- Product Height: 2.17 in [5.5 cm]
- Internal Ports: 1 - USB A Female
- Product Length: 4.72 in [12 cm]
- Maximum Data Transfer Rate: 480000000 Mbits/Sec
- Carton Quantity: 50
- Industry Standards: EHCI
- Shipping (Package) Weight: 0.24 lb [0.11 kg]
- Microsoft WHQL Certified: Yes
- Minimum Processor Requirements: PC - Intel Pentium 2 at 400MHz or faster, Intel Celeron at 900MHz or faster, AMD Athlon of any speed

Mac - G3 original processor or faster

- OS Compatibility: Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.2.6 or OS 10.2.8 Mac OS 10.2.6 or OS 10.2.8

