

4 Port PCI RS232 Serial Adapter Card with 16550 UART

StarTech ID: PCI4S550N



The PCI4S550N 4-port PCI Serial card turns an available PCI slot into four RS232 serial ports - a cost-effective solution for connecting any new or old serial peripheral, with support for data transfer rates of up to 115Kbps.

The PCI Serial card is a perfect solution for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system without having to upgrade your peripheral devices for compatibility with newer standards (e.g. USB).

Saving time and hassle, the Serial PCI card is plug-and-play ready, and can be installed in minutes, supporting Windows® 7, Server 2008 R2, Vista, XP, ME, 2000, 98, 95, NT4, 3.1, DOS® and Linux® operating systems. Plus, the serial card offers IRQ sharing to help ensure stability and consistent performance, guaranteeing convenient, hassle-free connections.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications

- **Manufacturing** (CNC machinery, process control equipment, bar code scanners, serial printers)
- **POS** (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- **Consumer** (modems, PDAs, digital cameras, printers)
- **Security** (UPS control, access key panels, video cameras, card readers, modems)
- **Casino** (video lottery terminals, slot machines)
- **Environmental Control** (lighting, temperature, clocks)
- **Hospital** (patient monitoring equipment, nurses' stations, modems)
- **Hotel Front Desk** (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- **Hospitality/Restaurant** (credit card/debit card reader, serial printers)
- **ISDN Networking**

Features

- Supports the RS-232 serial interface
- Includes drivers for Linux® and all versions of Windows®
- IRQ sharing saves resources and eliminates conflicts
- 16 byte FIFO buffer ensures fast data transfer while multitasking
- 5, 6, 7, 8-bit characters selection
- Even, odd, no parity, or force parity generations

Technical Specifications

Warranty	Lifetime
Ports	4
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile
Port Style	Integrated on Card
Industry Standards	PCI 2.1
Chipset ID	ASIX/MosChip - MCS9845CV
Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V; 32-bit) Male
External Ports	4 - DB-9 (9 pin; D-Sub) Male
Maximum Data Transfer Rate	115.2 Kbps
Serial Protocol	RS-232
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), XP Embedded, POS Ready 2009, Embedded System 2009, CE 5.0/6.0, 2000, 98SE, 95, DOS Windows® Server 2008 R2, 2003(32/64) Linux
Product Length	4.7 in [120 mm]
Product Width	0.8 in [20 mm]
Product Height	4.7 in [120 mm]
Product Weight	7.2 oz [204 g]
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in Package	1 - 2 Port PCI 16550 Serial Card
Included in Package	1 - Bracket with 2 DB9 Ports
Included in Package	1 - Driver CD
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

