

1 Port 10/100 Mbps Parallel Network Print Server

StarTech ID: PM1115P



This 10/100 Mbps Print Server lets you connect a Parallel printer to your Fast Ethernet (10/100Mbps) network, allowing you to share the printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The parallel print server can be installed in minutes and features remote web-based management for simple configuration. The print server features a small footprint design that saves valuable desk space, and can be connected directly into the parallel printer Centronics port and connected to a Fast Ethernet network using standard network cable (RJ45 terminated).

Providing dependable parallel printer sharing, this 10/100Mbps Print Server is backed by StarTech.com's 2-year warranty.

Applications and Solutions

- Connects your Ethernet network to one Parallel printer
- PM1115P offers network printing solution for home, small office, educational & government institutions and any other environments that require printer sharing

Features

- Compact and light weight print server only weighs 2.4 ounces
- Compliant with IEEE 1284, IEEE 802.3 & IEEE 802.3u standards
- Configurable using a Web based browser or a Windows based configuration
- Connects directly to the Centronics port of your printer
- Easy setup and configuration
- Eliminates the need to purchase additional printers for individual workstations
- Share 1 printer with computers connected to a home or small office network
- Support SNMP for remote printer management and works with any SNMP based application to access and manage
- Supports 10/100 Mbps fast Ethernet network

Technical Specifications

- Warranty: 2 Year warranty
- Color: Beige
- Connector Types: 1 - Centronics 36 Male
- Connector Types: 1 - RJ45 Female
- Enclosure Type: Plastic
- Product Height: 22
- LED Indicators: 1 - LAN
- LED Indicators: 1 - Status
- LED Indicators: 1 - Activity
- Product Length: 55
- Number of Ports: 1
- Power Adapter - Amperage: 2
- Power Adapter - DC Voltage: 5 DC
- Center Tip Polarity: Positive
- Supported Protocols: AppleTalk
- Supported Protocols: IPX/SPX
- Supported Protocols: NetBEUI
- Supported Protocols: SMNP
- Supported Protocols: TCP/IP
- Carton Quantity: 20

- Remote Management Ability: Yes
- Shipping (Package) Weight: 1.15 lb [0.52 kg]
- Product Weight: 67
- Product Width: 50
- OS Compatibility: Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS X and up

