

3 Port 2b 1a PCI 1394b FireWire Adapter Card with DV Editing Kit

StarTech ID: PCI1394B_3



The PCI1394B_3 3-Port PCI FireWire Adapter Card turns a PCI slot into 2 FireWire 800 (IEEE 1394b) ports and 1 FireWire 400 (IEEE 1394a) port - a cost-effective solution that lets you connect FireWire 800 devices, as well as older FireWire 400 devices to your desktop computer.

A versatile FireWire solution, the adapter card works in both 5v and 3.3v PCI slots and in 64-bit and 32-bit operating environments, making it easy to create a high-speed laptop digital media center, or connect demanding FireWire peripheral devices such as portable hard drives, DV camcorders, digital cameras and CD-RW/DVD-RW drives.

This high quality adapter card is designed to provide reliable FireWire 800 and FireWire 400 connections, and is backed by StarTech.com's Lifetime Warranty.

Applications

- Add a high-speed FireWire port to a desktop without any FireWire ports
- Connect a digital camera to a PCI/PCI-X enabled desktop to download photos and video
- Connect a high-speed external hard drive to an PCI/PCI-X enabled system

Features

- Two FireWire 800 ports with support for data transfer rates up to 800 Mbps
- One FireWire 400 port with support for transfer rates up to 400 Mbps
- Compliant with IEEE 1394-1995, 2000, 1394b and OHCI 1.1 standards
- Compliant with PCI revision 2.2 specifications
- Compatible with 3.3V/5V, 32/64-bit PCI or PCI-X slots
- Plug-and-Play and Hot-Swap compatible
- Includes Video Editing kit: Ulead Video Studio SE and FireWire cable

Technical Specifications

Warranty	Lifetime
Ports	3
Interface	FireWire 400 (1394a)
Bus Type	PCI/ PCI-X (5 / 3.3V)
Card Type	Standard Profile
Industry Standards	PCI 2.2, OHCI, IEEE-1394B, IEEE-1394A, IEEE-1394
Chipset ID	Texas Instruments - 3AA651W
Connector Type(s)	1 - PCI/ PCI-X (Universal 3.3 & 5V; 64-bit) Male
External Ports	1 - Firewire 400 (6 pin; IEEE 1394a) Female
External Ports	2 - Firewire 800 (9 pin; IEEE 1394b) Female
Maximum Data Transfer Rate	800 Mbps
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), Mac OS 10.2.4 and up, and Linux
Product Length	6.6 in [167 mm]
Product Width	0.7 in [18 mm]
Product Height	3.9 in [99 mm]
Product Weight	3.1 oz [89 g]
System and Cable Requirements	Unused PCI slot
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - PCI FireWire Card
Included in Package	1 - FireWire Cable
Included in Package	1 - Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

