

## 4 port PCI 1394a FireWire Adapter Card - 3 External 1 Internal

StarTech ID: *PCI1394MP*



This 4 Port (3 External/1 Internal) PCI 1394 FireWire Adapter Card lets you connect iPods, MP3 players, portable drives, digital camcorders and more to your desktop computer.

The FireWire adapter card supports hot-swapping, so you'll be able to plug, unplug, and swap your FireWire peripherals with ease.

Guaranteed to work with both PCs and Macs, the 4 port PCI FireWire Adapter Card is backed by StarTech.com's Lifetime Warranty and FREE LIFETIME tech support. Plus, the adapter provides both standard profile and low profile/half-height brackets for adapting to slimline or small form factor system applications.

Please Note: If you require digital video editing software, StarTech.com offers a complete FireWire kit with our [PCI1394\\_4](#), [PCI1394\\_2](#) and [PCI1394\\_2LP](#) cards. This software is compatible with Windows operating systems only.

WHQL Certified - Designed to work with Microsoft Windows XP

### Applications

- Add a high-speed FireWire port to a full or small form factor desktop without any FireWire ports
- Connect a digital camera to a desktop with a PCI slot to download photos and video
- Connect a external FireWire hard drive or optical drive to a PCI-enabled system

## Features

- 3 external, 1 shared internal FireWire400 port, with supported data transfer rates up to 400 Mbps
- Compliant with IEEE 1394a - 2000 as well as 1394-1995 standards
- Includes Low Profile installation bracket
- Plug-and-Play and hot-swap compatible

## Technical Specifications

Warranty	Lifetime
Ports	3
Interface	FireWire 400 (1394a)
Bus Type	PCI (5 Volt)
Card Type	Standard Profile (LP bracket incl.)
Industry Standards	IEEE 1394a
Industry Standards	OHCI
Industry Standards	PCI 2.1
Chipset ID	Texas Instruments - TSB12LV26
Connector Type(s)	1 - PCI (5V; 32-bit) Male
Internal Ports	1 - Firewire 400 (6 pin; IEEE 1394a) Female
External Ports	3 - Firewire 400 (6 pin; IEEE 1394a) Female
Maximum Data Transfer Rate	400 Mbps
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), Linux, and Mac OS 8.6 and up
Microsoft WHQL Certified	Yes
Product Length	4.8 in [12.3 cm]
Product Width	0.7 in [18 mm]
Product Height	3.1 in [8 cm]
Product Weight	2.5 oz [70 g]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - PCI FireWire Card
Included in Package	1 - Low Profile Bracket
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

