

1 Port PCI Low Profile RS232 Serial Adapter Card with 16550 UART

StarTech ID: *PCI1S550_LP*



This 16550 Serial PCI Card can be installed in a computer PCI slot to add an RS232 serial port - a cost-effective solution for connecting any new serial device or old legacy serial device, with data transfer rates of up to 115.2 Kbps. The serial card features a low profile/half-height bracket, suitable for installation in low profile/small form factor computer cases.

Perfect for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system, the PCI Serial card supports IRQ sharing and operates flawlessly with Windows® 7, Server 2008 R2, Vista, XP, Server 2003, 2000, ME, 98, 95, NT4, 3.1, DOS® and Linux®.

Saving time and hassle, the PCI serial card can be connected in minutes through simple plug and play installation and is backed by StarTech.com's lifetime warranty and FREE LIFETIME tech support.

Applications and Solutions

- **Manufacturing** (CNC machinery, process control equipment, bar code scanners, serial printers)
- **POS** (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- **Consumer** (modems, PDAs, digital cameras, printers)
- **Security** (UPS control, access key panels, video cameras, card readers, modems)
- **Casino** (video lottery terminals, slot machines)
- **Environmental Control** (lighting, temperature, clocks)
- **Healthcare** (patient monitoring equipment, nurses' stations, modems)
- **Hotel Front Desk** (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- **Hospitality/Restaurant** (credit card/debit card reader, serial printers)
- **ISDN Networking**

Features

- Supports the RS-232 serial interface
- 16 byte FIFO buffer ensures fast data transfer while multitasking
- IRQ sharing saves resources and eliminates conflicts
- OS Support: DOS, Windows 95/ 98SE/ ME/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI (5 Volt)
- Chipset ID: NetMos NM9820CV
- External Ports: 1 - DB 9-pin Serial Male
- Product Height: 2.17 in [5.5 cm]
- Product Length: 4.72 in [12 cm]
- Maximum Data Transfer Rate: 920000 Kbits/Sec
- Number of Ports: 1
- Carton Quantity: 50
- Shipping (Package) Weight: 0.27 lb [0.12 kg]
- OS Compatibility: DOS, Windows 95/ 98SE/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/

Server 2008 R2, Linux, and Mac OS 10.4.x and up

Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS

