




### Installation Guide

**WARNING!** Computer equipment can be severely damaged by static electricity. Be sure that you are properly grounded before opening your computer case or touching your hard drive. StarTech.com recommends that you wear an anti-static strap when installing any computer component. If an anti-static strap is unavailable, discharge yourself of any static electricity build-up by touching a large grounded metal surface (such as the computer case) for several seconds.

1. Remove the computer cover. For more detailed instruction on how to perform this step, please refer to the documentation that was included with your computer at the time of purchase.
2. Locate an empty PCI slot and remove the metal bracket covering the accompanying empty port/socket.
3. Position the card above the open PCI slot, ensuring that the card is properly aligned with the slot. Insert the card firmly into the slot, distributing force evenly across the length of the board, then fasten the metal bracket to the computer case (using the screw removed in step #2).
4. Once PCI2MPCIB has been secured within the PCI slot, align the Mini PCI card you wish to install with the Mini PCI slot, so that the Mini PCI card is on a slight angle (~ 45°) with the PCI2MPCIB board (see fig. 1-1). With the Mini PCI card still on a slight angle, insert the card into the slot until the gold connectors at the bottom of the card are no longer visible (now hidden by the Mini PCI slot).
5. Gently, press the Mini PCI card towards PCI2MPCIB until the retaining notches on the card snap into the plastic retaining tabs (see fig. 1-2). Once PCI2MPCIB is secured within the PCI slot, replace the computer cover and re-connect all power to the computer.



Retaining Notches

# Specifications

<b>Bus Type</b>	32-bit PCI 3.3v/5v
<b>Connectors</b>	1 x MiniPCI Type III (124 pin)
<b>Product Weight</b>	50 g (1.77 oz )
<b>Product Dimensions (W x H x L)</b>	137 mm (5.39") x 21 mm (0.83") x 121 mm (4.76" )

## Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

## Warranty Information

This product is backed by a lifetime warranty. In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

## Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product.

Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.