


2S1P PCI Serial Parallel Combo Card with 16550 UART

StarTech ID: PCI2S1P



The PCI2S1P PCI Serial/Parallel Combo Card turns a PCI slot into two external 16C550 serial ports and one external EPP/ECP parallel port - an all-in-one solution that gives you both parallel and serial connections while taking up only one PCI slot.

Suitable for installation in a small form factor computer, the PCI serial/parallel card includes an optional low profile/half-height mounting bracket that makes installation easy.

The serial/parallel combo card is PCI plug and play ready and supports IRQ sharing for fast, simple installation. The combo card is supported in virtually any Microsoft Windows operating environment (Windows® 7, Server 2008 R2, Vista, XP, ME, 2000, 98, 95 and NT4), and is backed by a StarTech.com Lifetime Warranty and free lifetime technical support.

Applications and Solutions

- Self service automated machines and kiosks to control serial devices such as scales, touchscreens, magnetic card readers, bar code scanners, receipt printers, label printers
- POS retail applications in grocery stores, and any other retail store to control keyboards, cash drawers, receipt printers, card readers / card swipes, scales, and elevated displays on poles

- Bank teller workstations in either full profile or low profile versions to control their serial devices such as cash drawers, card readers / card swipes, printers, keypads / pinpads, pen pads
- Standard ATM automated teller machines to control keypads, receipt printer, card readers / card swipes, touchscreen LCD's, camera control, etc.
- Used to control multiple surveillance / security cameras in a parking structure, office building, etc.

Features

- Two 16C550 serial ports with data transfer up to 460.8 Kbits/sec
- One EPP/ECP parallel port with data transfer up to 1.5 Mbits/sec
- Includes optional low profile/half-height mounting bracket
- Parallel port supports EPP, ECP, SPP and BPP
- IRQ sharing eliminates conflicts between multiple cards
- Compatible OS: DOS, Windows 95/ 98SE/ ME/ XP(32/64bit)/ Vista(32/64bit)/ 7 (32/64bit), Linux

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI (5 Volt)
- Connector Types: 1 - DB25 Female
- Connector Types: 2 - DB9 Male
- Product Height: 2.17 in [5.5 cm]
- Product Length: 4.72 in [12 cm]
- Maximum Data Transfer Rate: Up to 1.5 Mbits/sec.
- Number of Ports: 2
- Carton Quantity: 50
- Shipping (Package) Weight: 0.49 lb [0.22 kg]
- Chipset ID: MosChip MCS9835
- OS Compatibility: DOS, Windows 95/ 98SE/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.4.x and up
Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS/ CE 5.0/ CE 6.0

