


## **4 Port PCI RS232 Serial Adapter Card with 16550 UART**

*StarTech ID: PCI4S550N*



The PCI4S550N 4-port PCI Serial card turns an available PCI slot into four RS232 serial ports - a cost-effective solution for connecting any new or old serial peripheral, with support for data transfer rates of up to 115Kbps.

The PCI Serial card is a perfect solution for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to your system without having to upgrade your peripheral devices for compatibility with newer standards (e.g. USB).

Saving time and hassle, the Serial PCI card is plug-and-play ready, and can be installed in minutes, supporting Windows® 7, Server 2008 R2, Vista, XP, ME, 2000, 98, 95, NT4, 3.1, DOS® and Linux® operating systems. Plus, the serial card offers IRQ sharing to help ensure stability and consistent performance, guaranteeing convenient, hassle-free connections.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Applications and Solutions

- **Manufacturing** (CNC machinery, process control equipment, bar code scanners, serial printers)
- **POS** (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- **Consumer** (modems, PDAs, digital cameras, printers)
- **Security** (UPS control, access key panels, video cameras, card readers, modems)
- **Casino** (video lottery terminals, slot machines)
- **Environmental Control** (lighting, temperature, clocks)
- **Hospital** (patient monitoring equipment, nurses' stations, modems)
- **Hotel Front Desk** (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- **Hospitality/Restaurant** (credit card/debit card reader, serial printers)
- **ISDN Networking**

## Features

- Supports the RS-232 serial interface
- Includes drivers for Linux® and all versions of Windows®
- IRQ sharing saves resources and eliminates conflicts
- 16 byte FIFO buffer ensures fast data transfer while multitasking
- 5, 6, 7, 8-bit characters selection
- Even, odd, no parity, or force parity generations

## Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI / PCI-X (5 / 3.3V)
- External Ports: 4 - DB 9-pin Serial Male
- Product Height: 2.91 in [7.4 cm]
- Product Length: 4.72 in [12 cm]
- Maximum Data Transfer Rate: 921000 Kbits/Sec
- Number of Ports: 4
- Carton Quantity: 50
- Industry Standards: PCI 2.1
- Shipping (Package) Weight: 0.46 lb [0.21 kg]
- Product Weight: 7.2 oz [204 g]
- Chipset ID: MosChip MCS9845
- OS Compatibility: DOS, Windows 95/ 98SE/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 10.4.x and up  
Windows XP Embedded/ POS Ready 2009/ Embedded System 2009 OS/ CE 5.0/ CE 6.0

