

42U 42in Server Rack Cabinet

StarTech ID: RK4242BK



The RK4242BK 42U 42in Server Rack Cabinet features an all steel, welded frame construction that provides durable, high quality rack storage at an affordable price.

This modular 42U cabinet helps save space in the server room by using an innovative split rear door, and is designed to suit any server room footprint design, while housing any standard 19in rackmount equipment. Plus, adjustable front and rear rails allow you to shift mounting depths to suit almost any piece of rackmount equipment.

To help optimize ventilation, the cabinet offers steel mesh doors with wide perforation, and includes an integrated cable management system that helps keep the inside of the cabinet neat. Plus, the rack rail spacing is clearly marked, making it easy to plan and install equipment within the cabinet.

This high quality 42U Server Rack Cabinet is backed by StarTech.com's Lifetime Warranty.

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Extra deep 42" enclosure accommodates all full size rackmount equipment
- Includes lockable front and rear doors, and dual lock side panels
- Split rear door minimizes the required access space behind the cabinet
- Includes integrated cable management system, casters, leveling feet, mounting screws
- Front and rear doors easily removable
- All steel, welded frame construction
- Ships fully assembled

Technical Specifications

Warranty	Lifetime
Casters	Included
U Height	42U
Frame Type	Enclosed Cabinet
Wallmountable	No
Front Door Type	Steel Mesh
Side Panel Type	Solid Steel
Back Door Type	Steel Mesh
Key Lock	Yes
Industry Standards	EIA RS310-D
Fan(s)	No
Weight Capacity	2210 lb [1000 kg]
Color	Black
Internal Width	18.3 in [465 mm]
Internal Depth	34 in [863.6 mm]
External Width	23.8 in [605 mm]
External Height	77.5 in [1968 mm]
External Depth	42.1 in [1070 mm]
Product Weight	311.6 lb [141 kg]
Height with Casters	78.7 in [1998 mm]
Flat Pack	No
Shipping (Package) Weight	335.9 lb [152 kg]
Included in Package	1 - 42U 42" DuraRak
Included in Package	2 - 42" Enclosure sides (installed)
Included in Package	1 - Integrated cable management system
Included in Package	4 - Leveling feet
Included in Package	4 - Cable access caps
Included in Package	1 - Allen key for skid removal
Included in Package	1 - Set of keys for doors and sides
Included in Package	1 - Package of mounting screws

Certifications, Reports and Compatibility



