

## 2.5in Black USB 2.0 External Hard Drive Enclosure for SATA HDD

StarTech ID: SAT2510BU2



This external hard drive enclosure transforms a 2.5in SATA (SATA, SATA II, SATA III) hard drive or SSD into the perfect portable storage solution.

Ideal for storing digital multimedia and other demanding applications, the enclosure lets you get the most out of your hard drive, connecting to a host computer using USB 2.0 (also backward compatible with USB 1.1), for maximum data transfer rates of 480Mbps. Large capacity drives (tested with up to 1TB) can be used to greatly enhance your computer's storage/backup capabilities.

Plus, the external hard drive enclosure includes a USB Y-cable, that when both USB male connectors are connected to the host computer eliminates the need for an external power adapter.

### Applications

- Create a fast, ultra portable external storage solution for laptops or netbooks
- Add-on storage to any USB enabled computer system
- Backup data to an external storage device
- Retrieve data from old laptop drive, or turn the unused drive into additional external storage space

## Features

- Light-weight, durable aluminum construction
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Power/activity LED
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" form factor SATA hard drives (HDD) and solid state drives (SSD)
- Powered directly from the USB ports
- Compact, portable design
- Includes a protective carrying pouch

**Technical Specifications**

Warranty	2 Years
Interface	USB 2.0
Number of Drives	1
Drive Size	2.5in
Drive Type	SATA
Drive Installation	Fixed
Fan(s)	No
Chipset ID	Sunplus - SPIF225A
Connector Type(s)	1 - USB Mini-B (5 pin) Female
Maximum Data Transfer Rate	480Mbps
RAID	No
Max Drive Capacity	Currently tested with up to 1TB 5400 RPM hard drives
OS Compatibility	Windows 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8 (32/64-bit) Mac OS 10.4/ 10.5/ 10.6/ 10.7/ 10.8 Linux
Color	Black
Enclosure Type	Aluminum
Max Drive Height	0.4 in [9.5 mm]
Product Length	4.7 in [120 mm]
Product Width	3 in [75 mm]
Product Height	0.4 in [10 mm]
Product Weight	2.2 oz [62.1 g]
LED Indicators	1 - Green: Power / Red: Drive Activity
Power Adapter Included	No
Input Voltage	5 DC
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in Package	1 - 2.5" SATA Enclosure
Included in Package	1 - USB 2.0 Y-Cable
Included in Package	1 - Screw Kit
Included in Package	1 - Mini Screwdriver
Included in Package	1 - Protective Case

Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

