

5.25in Bay Removable 3.5in SATA HDD Enclosure

StarTech ID: SAT3510U2REM



This USB to SATA External Hard Drive Enclosure turns a 3.5in SATA (SATA, SATA II, SATA III) hard drive into a dual purpose add-on external storage and internal removable hard drive storage solution!

Supporting the latest generation of Serial ATA hard drives, this external hard drive enclosure is the ideal solution for large volume data offloads, digital video recording, surveillance systems, audio editing (no fan so noiseless), external storage, or a simple way to swap storage between your laptop and desktop computers.

Simply install the provided bay enclosure bracket into any 5.25in drive bay on the host computer, and enjoy the convenience of removable storage that can be ejected from one computer and connected to another as a conventional external hard drive.

Applications

- Professionals working with large files who need to transport them between computers/locations without a network
- Easily work on and store large presentations or demos from your desktop, then transport it to a clients location without having to transfer files between drives
- Business professionals who need first hand access to their office data while traveling
- Users who need both fast internal storage and portable external storage

Features

- Front mount drive bay installs into any standard 5.25" bay
- Unique enclosure design allows it to be used as an internal removable SATA drive or as a regular external USB enclosure
- Push lever drive ejection from the front mount bay
- Durable aluminum construction for the drive enclosure chassis
- Power/Activity LED indicator
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 3.5" form factor SATA hard drives
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

Warranty	2 Years
Interface	USB 2.0
Number of Drives	1
Drive Size	3.5in
Drive Type	SATA
Drive Installation	Removable
Fan(s)	No
RAID	No
General Specifications	
General Specifications	1x 5.25" bay & SATA support
General Specifications	1x LP4 Male
General Specifications	1x SATA Data 7 Pin Female
General Specifications	1x SATA Data 7 Pin Male
General Specifications	1x SATA Power 15 Pin Female
General Specifications	1x USB B Female (External)
General Specifications	3 Gbps via SATA
General Specifications	3.5" SATA (SATA, SATA II, SATA III) hard drives tested up to 2.0 TB in size
General Specifications	480 Mbps via USB
General Specifications	Any available USB port
OS Compatibility	Windows ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 9.x and up
Color	Silver
Enclosure Type	Aluminum
Product Length	7.8 in [198 mm]
Product Width	4.4 in [113 mm]
Product Height	1.3 in [32 mm]
Product Weight	17.6 oz [500 g]
LED Indicators	1 - Power and activity
Power Adapter Included	Yes
Shipping (Package) Weight	3 lb [1.3 kg]
Included in Package	1 - Drive Bay Frame
Included in Package	1 - External Enclosure
Included in Package	1 - SATA Data Cable

- Included in Package 1 - USB Cable
- Included in Package 1 - Mounting Hardware
- Included in Package 1 - Power Cord
- Included in Package 1 - Power Adapter
- Included in Package 1 - Manual

Certifications, Reports and Compatibility

