

5.25in Silver eSATA USB 2.0 to SATA Optical Drive Enclosure

StarTech ID: SAT5210U2E



This versatile drive enclosure offers a cost-effective way to turn any SATA II 3.5in hard drive (up to 1.5TB) or 5.25in optical drive (Blu-ray DVDRW, CD-ROM, CD-RW, DVD-ROM, DVD-RW), into an external solution.

The drive enclosure can be connected to a host computer through either USB 2.0 or eSATA, and supports the full capability of both interfaces (maximum data transfer capability up to 3 Gbps with eSATA, up to 480 Mbps through USB 2.0).

To help ensure dependable drive operation, the enclosure provides a sturdy yet attractive aluminum casing and a 40mm fan to help keep the installed hard drive or optical drive cool.

Drives can be installed in the enclosure in minutes, and includes the added convenience of a stereo headphone jack for computer-free CD playback.

Applications

- Turn any internal SATA III drive into an external DVD/CD drive or storage.
- Add external DVD/CD burning capability to notebooks and desktops with USB or eSATA connectivity.

Features

- Equipped with USB 2.0 and eSATA interfaces for maximum data transfer, and versatility
- Aluminum casing and 40mm fan for maximum heat dissipation
- Quick and easy installation
- Stereo headphone jack for computer free CD playback
- Full plug and play support through USB 2.0 interface
- Allows 3.5" SATA III (SATA 150/300) Hard Drives (including 1.5 terabyte) and 5.25" SATA Optical Drive in one enclosure.

Technical Specifications

Warranty	2 Years
Drive Installation	Fixed
Drive Size	5.25in
Drive Type	SATA
Fan(s)	Yes
Fans	1 - 40 mm
Interface	USB 2.0 & eSATA
Number of Drives	1
Drive Connectors	1 - SATA Data & Power Combo (7+15 pin) Receptacle
Host Connectors	1 - eSATA (7 pin; Data) Plug
Host Connectors	1 - USB B (4 pin) Female
Max Drive Capacity	Currently tested with up to 1.5TB 5400 RPM 3.5" hard drives
Type and Rate	SATA II (3 Gbps)
Type and Rate	USB 2.0 - 480 Mbit/s
OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit), Mac OS 9x and up, and Linux
Color	Silver
Enclosure Type	Aluminum
Product Length	10.2 in [259 mm]
Product Width	6.5 in [166 mm]
Product Height	2.3 in [58 mm]
Product Weight	32.8 oz [930 g]
LED Indicators	1 - Power LED (Green)
Center Tip Polarity	Positive
Output Current	2A
Output Voltage	12 DC
Power Adapter Included	Yes
Shipping (Package) Weight	3.4 lb [1.6 kg]
Included in Package	1 - 5.25" Drive Enclosure
Included in Package	1 - USB Cable
Included in Package	1 - Power Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

