

4 Port Tower Style PS/2 KVM Switch Kit with Cables

StarTech ID: SV411KT



This 4-port tower style KVM Switch Kit lets you control multiple PS/2 computers from a single console (keyboard, mouse, monitor), saving equipment costs while providing a convenient operating platform.

A perfect console-sharing solution for SOHO, help desks and call centers, the KVM switch supports display resolutions of up to 1920x1440 as well as plug-and-play connectivity, which eliminates the hassle of having to power down computers to be connected to the switch. To ensure error-free bootups, the KVM switch supports PS/2 keyboard and mouse emulation.

The KVM switch offers both keyboard hotkey and front panel push-button control, and features a compact and lightweight mini-tower design with rear panel cable connections, saving valuable workspace.

Providing an out-of-the-box KVM solution, the tower style switch includes four 3-in-1 tangle-free cables and is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Applications and Solutions

- Lets you instantly control four PS/2 computers from a single keyboard, mouse and monitor
- Compatible with desktops, workstations, servers, and laptops
- Useful for call centers, help desks, education environments, home gamers and PC enthusiasts

Features

- Unique 3-in-1 cables prevent keyboard and mouse connectors from becoming loose
- Lightweight, compact mini tower
- Rear cable connections keep your desktop neat and tangle free
- Supports PS/2 keyboard and mouse emulation for error-free PC bootup
- Hot pluggable keyboard and mouse ports allow easy connections without having to reboot your systems
- Compatible with all operating systems
- Supports high VGA resolution of up to 1920x1440
- Power-free operation, draws power from attached computers and requires no external power adapters
- Port selection using push button or keyboard commands
- Supports Logitech Mouseman, and MS Intellimouse (Ver 2.0 and earlier).
- Supports PS/2 keyboard and mouse emulation for error-free PC bootup
- Draws power from computer, requiring no external power adapter

Technical Specifications

- Warranty: 2 Years
- Auto Scan: 3, 8, 15 & 30 seconds
- Product Depth: 3.94 in [100 mm]
- Product Height: 4.96 in [12.6 cm]
- LED Indicators: Port Status
- Product Length: 3.94 in [10 cm]
- Maximum Number of Computers: 4
- Maximum Analog Resolutions: 1920x1440
- Maximum Number of Users: 1
- OS Compatibility: OS Independent
- Carton Quantity: 6
- Industry Standards: DDC2B
- Shipping (Package) Weight: 2.7 lb [1.22 kg]
- Product Weight: 7.2 oz [204 g]
- Product Width: 1.97 in [5 cm]

