

InfoSafe External Slim USB 2.0 DVD +/- RW Dual Layer Drive

StarTech ID: SLIMDVDRW8U2



The perfect notebook accessory, SLIMDVDRW8U2 features a Panasonic drive that gives you the freedom to play DVD's and CD's, or copy and transfer data at impressive speeds, without needing a built-in DVD-RW drive. Providing 5x DVD-RAM write speeds, 8x (DVD+RW), and 6x (DVD-RW), this is one notebook accessory that will really save you time and hassle. Plus, the attractive, discreet casing of this drive blends perfectly with your notebook computer, and its thin, yet durable design fits handily into your carrying case for times when you are on the move!

Applications

- Ideal for users without DVD/CD drive in their laptop or notebook
- For users who require DVD/CD “burning” capability with laptop/notebook – may just have older ROM drive.
- A great server room accessory that provides optical drive support to servers and data storage systems where conventional drives are not supported

Features

- Tray-loading multi-format DVD drive:
- 5X DVD-RAM Writing
- 8X DVD-R Writing
- 6X DVD-RW Writing
- 8X DVD+R Writing
- 8X DVD+RW Writing
- 4X DVD-R DL Writing
- 4X DVD+R DL Writing
- 24X CD-R Writing
- 16X CD-RW Writing
- 8X DVD-ROM Reading
- 24X CD-ROM Reading
- Supports USB 2.0 and backwards compatible to USB 1.1
- Supports mini CD's which are popular for drivers
- DVD Burning software (Nero 7 Essentials)
- No power adapter required for CD/DVD-ROM use
- Hot swappable plug and play

Technical Specifications

Warranty	2 Years
Connector Type(s)	1 - USB B (4 pin) Female
General Specifications	ATA(IDE) / ATAPI CD-R, CD-RW, DVD-R, DVD-RW, DVD Super-Multi
General Specifications	2MB
General Specifications	4.7GB / 8.5GB (DL)
General Specifications	External Slim 5.25" Enclosure with DVD Drive
General Specifications	FCC(power adapter)/UL/CUL(power adapter)/CE/RoHS
General Specifications	Soft Read Error (Less than 10 ⁻⁹) Hard Read Error (Less than 10 ⁻¹²)
General Specifications	Supports USB 2.0 and USB 1.1
General Specifications	UL/CE/TUV/CB/RoHS
General Specifications	Windows: 98SE (Setup driver CD incl.), ME, 2000, XP, Vista (Excl. Nero SW), MAC OS 10.4 or higher
Color	Black
Enclosure Type	Plastic
Product Length	6.5 in [165 mm]
Product Width	5.3 in [135 mm]
Product Height	0.9 in [23 mm]
Product Weight	12.4 oz [350 g]
LED Indicators	1 - Read/Write
Power Adapter Included	Yes
Operating Temperature	5 ~ 50 degrees
Storage Temperature	-30 ~ 65 degrees
Shipping (Package) Weight	1.9 lb [0.9 kg]
Included in Package	1 - External DVD Drive Enclosure
Included in Package	1 - Tray-Loading DVD Super-Multi Drive
Included in Package	1 - DVD Burning Software
Included in Package	1 - USB 2.0 Cable
Included in Package	1 - Power Adapter
Included in Package	1 - CD (W98SE Driver)
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

