

## 15 ft 3-in-1 Universal PS/2 KVM Cable

StarTech ID: SVPS23N1\_15



StarTech.com's universal series PS/2 KVM switch cables prevent tangles and keep your workspace neat while delivering excellent performance with your StarTech.com StarView or other KVM switch.

This 15ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and durable performance. Like all StarTech.com cables, this product comes with a Lifetime warranty.

### Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

TrippLite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

### Applications

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some non-StarView models may require gender changing cable adapters.)

### Features

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite cores at both ends of video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

## Technical Specifications

|                           |  |
|---------------------------|--|
| Warranty                  | Lifetime   |
| Connector A               | 1 - VGA (15 pin; High Density D-Sub) Male  |
| Connector A               | 2 - PS/2 (6 pin; Mini-DIN) Male  |
| Connector B               | 1 - VGA (15 pin; High Density D-Sub) Female  |
| Connector B               | 2 - PS/2 (6 pin; Mini-DIN) Male  |
| Cable Length              | 15 ft [4.6 m]  |
| Shipping (Package) Weight | 1.9 lb [0.9 kg]  |
| Included in Package       | 1 - 15 FOOT PS/2 3-IN-1 KVM SWITCH CABLE   |
| Included in Package       | 1 - DB15 male/male gender changer (GC15HSM)  |
| Included in Package       | 1 - metal part of thumbscrew must be 1.17in(3cm)                                   |
| Included in Package       | 1 - THUMBSCREWS MUST BE 1.93 inches long (4.9cm) THUMBSCREWS MUST BE 1.93in(4.9cm) |

## Certifications, Reports and Compatibility

