

USB DVI VGA External Dual or Multi Monitor Video Adapter

StarTech ID: USB2DVIE



This USB to DVI/VGA Multi-Monitor External Video Adapter acts as an external video card for any USB 2.0 laptop or desktop computer. The external video adapter converts a USB 2.0 port into a DVI-I port - providing high quality dual display or multi-monitor capability that allows you to mirror or extend the desktop shown on the existing display as needed.

For an even more versatile multi display configuration, up to five USB to DVI/VGA video adapters can be connected to the same computer simultaneously, allowing for a total of five USB connected DVI monitors to display video from a single computer.

The USB to DVI/VGA External Multi Monitor Video Adapter can also be connected to VGA monitors using the included DVI to VGA adapter, and can be connected to an HDMI display using a [DVI to HDMI Adapter](#) (HDMIDVIFM - Not included).

Applications

- Excellent solution for notebooks enabling the connection of multiple adapters to multiple displays (up to six monitors, including notebook display).
- Run multiple applications on different screens, check your email on one display and work on a document in the other.
- Run in extended mode where your desktop can span across multiple screens or mirror you image as if you were using a video splitter.

Features

- Add a secondary display adapter and extend your desktop/notebook display without taking apart your computer to install a new video card
- No power adapter required and easy to install
- Supports resolutions up to 1600x1200 and 1680x1050(for widescreen / format displays) @ 32 bits
- Acts as an external video card connected through USB 2.0

Technical Specifications

Warranty	2 Years
Memory	16MB RAM
Chipset ID	MCT Corp. Trigger 1
Output Signal	DVH (DVI Digital/Analog)
Connector A	1 - USB A (4 pin) Male
Connector B	1 - DVH (29 pin) Female
Supported Resolutions	Standard(16/32-bit) 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600 Widescreen 1920x1200(16-bit), 1920x1080(16-bit), 1680x1050(16/32), 1440x900(16/32), 1280x800(16/32), 1280x768(16/32)
Wide Screen Supported	Yes
OS Compatibility	Windows 2000/XP, Vista 32/64 bit
Color	Black
Enclosure Type	Plastic
Product Length	3.5 in [90 mm]
Product Width	1.9 in [48 mm]
Product Height	0.9 in [23.5 mm]
Product Weight	2.6 oz [73 g]
System and Cable Requirements	Available USB 2.0 port 1.2GHz or higher CPU 512MB RAM 30MB Hard Drive space
Note	Connect a maximum of five USB2DVIE adapters on a single PC
Shipping (Package) Weight	0.7 lb [0.3 kg]
Included in Package	1 - USB to DVI Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

