

USB VGA External Dual or Multi Monitor Video Adapter - High Resolution

StarTech ID: USB2VGA2



The USB2VGA2 USB VGA Adapter turns an available USB 2.0 port into an external video card VGA port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2VGA2 Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGA2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Optimal performance at 1680x1050 and ideal for use with 20" to 22" monitors or smaller
- Easy installation
- No power adapter required

Technical Specifications

Warranty	2 Years
Chipset ID	SiS - 315
Connector Type(s)	1 - USB A (4 pin) Male
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Supported Resolutions	Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600 Widescreen(16 bit): 1920x1200, 1920x1080 (16/32 bit): 1680x1050, 1440x900, 1280x800, 1280x768
OS Compatibility	Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)
Enclosure Type	Plastic
Cable Length	18 in [457.2 mm]
Product Length	4.3 in [110 mm]
Product Width	2 in [51 mm]
Product Height	0.9 in [24 mm]
Product Weight	3.2 oz [90 g]
System and Cable Requirements	One available USB 2.0 port
Shipping (Package) Weight	0.6 lb [0.3 kg]
Included in Package	1 - USB to VGA Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

