

**USB to VGA Multi Monitor External Video Adapter**  
*StarTech ID: USB2VGAE2*



The USB2VGAE2 USB VGA adapter is the perfect multi-monitor VGA solution - a replacement for our popular USB2VGAE that delivers improved performance and a sleek new design.

The USB video adapter features a small form factor as well as support for high-performance/ high resolution applications, turning an available USB 2.0 port into a VGA port. A cost-saving multi-monitor or dual display option that can be used as an external graphics card for either laptop or desktop applications.

The USB video adapter can be used with up to four additional (five total) USB2VGAE2 USB video adapters, creating multiple VGA connections that can be used to further extend or mirror the desktop shown on the existing display - all without having to open the computer case to add extra video cards.

Application Diagram

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## **Applications and Solutions**

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGAE2 device for each additional display
  - View large or multiple spreadsheets across multiple displays
  - A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
    - Connect multiple monitors to a single computer to create engaging multimedia presentations
    - Use the adapter to connect your PC to your television for showing family pictures and movies
    - Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
    - Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

## Features

- No power adapter required
- Optimal performance at 1440x900 (higher resolutions supported) and ideal for use with 17" to 19" monitors or smaller
- Works with desktop and laptop computers
- Includes easy to use software that allows for, multi-display management and EDID monitor detection for increased compatibility with displays
- Simple installation

## Technical Specifications

- Warranty: 2 Years
- Cable Length: 18 in [457.2 mm]
- Product Height: 1.97 in [50 mm]
- Product Length: 2.95 in [75 mm]
- Memory: 16MB SDRAM
- OS Compatibility: Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit); Drivers are WHQL certified
- Carton Quantity: 40
- Supported Resolutions: Standard(16/32 bit):

1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600

Widescreen(16/32 bit):

1680x1050, 1400x900, 1280x800, 1280x768, 1152x864, 1024x768, 800x600

- Shipping (Package) Weight: 22.59 oz [640 g]
- Product Weight: 2.82 oz [80 g]
- Product Width: 1.65 in [42 mm]
- System and Cable Requirements: One available USB 2.0 port

