

10 ft USB 2.0 Cable for Digital Cameras - A to 4 Pin Mini

StarTech ID: USBFA4S10



This high-quality Mini B USB 2.0 cable is a cost effective way to maximize the performance of your digital camera, MP3 player, PDA, or digital camcorder. With 480 Mbits/sec of reliable data transfer, you'll spend your time viewing and listening to your AV files, not waiting for them to download.

These cables use pure digital data transfer for sharper, more natural images and sound at higher speeds. Like all our cable products, these USB 2.0 cables are backed by StarTech.com's lifetime warranty.

Applications

- An Ideal replacement USB cable for transferring pictures, videos, MP3 files from you digital camera, digital camcorders, MP3 players, PDA and other portable devices to your laptop or desktop PC

Features

- The Mini B cable meets USB 2.0 requirements which is 40 times faster than USB 1.0
- Download pictures and MP3 files with fast data transfer rates of up to 480 Mbits/sec
- Suitable for a variety of digital cameras, camcorders and portable devices

Technical Specifications

Warranty	Lifetime
Connector A	1 - USB A (4 pin) Male
Connector B	1 - USB Mini (4 pin) Male
Maximum Cable Length	16.4 ft [5 m]
General Specifications	
General Specifications	10ft (3.05 m)
General Specifications	2.0
General Specifications	Connector 2: Mini B 4 pin (male)
General Specifications	Connector 1: 4 pin USB Type A (male)
General Specifications	Model # 3000Z
General Specifications	Model # 3100Z
General Specifications	Model # 315
General Specifications	Model # C-2040 Zoom
General Specifications	Model # C-2100 Zoom
General Specifications	Model # C-3000 Zoom
General Specifications	Model # C-3040 Zoom
General Specifications	Model # C-4040 Zoom
General Specifications	Model # D-100
General Specifications	Model # D-510 Zoom
General Specifications	Model # DiIMAGE 5
General Specifications	Model # DiIMAGE 7
General Specifications	Model # DiIMAGE 7i
General Specifications	Model # DSC-F505V
General Specifications	Model # DSC-S30
General Specifications	Model # DSC-S50
General Specifications	Model # DSC-S70
General Specifications	Model # DX3215
General Specifications	Model # DX3500
General Specifications	Model # DX3600
General Specifications	Model # DX3700
General Specifications	Model # DX3900
General Specifications	Model # DX4900
General Specifications	Model # E-10
General Specifications	Model # GC-QX3

General Specifications	Model # MVC-CD1000
General Specifications	Model # Olympus C-2100UZ
General Specifications	Model # Olympus C-3030Z
General Specifications	Model # Olympus C-700 UZ
General Specifications	Model # Olympus E-10
General Specifications	Model # Olympus E-20
General Specifications	Model #D-510
General Specifications	Model# 315xi
General Specifications	Nikon® Digital Camera:
General Specifications	PC and Mac
General Specifications	Up to 480 Mbits/sec
Color	Black
Product Length	10 ft [3 m]
Shipping (Package) Weight	0.1 lb [0.1 kg]

Certifications, Reports and Compatibility

